




Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Operating Temperature (Max): **150 °C**

Pre-Installed Lead: **Yes**

Wire Size: **22 AWG**

Wire Temperature (Max): **125 °C**

Features

Configuration Features

Pre-Installed Lead	Yes
--------------------	-----

Dimensions

Wire Size	22 AWG
-----------	--------

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	150 °C
Wire Temperature (Max)	125 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought



TE Part #1577616-1
TERMINAL, PEEK PIDG STRATO, 24-22AWG



TE Part #1577647-1
TERMINAL RT PIDG PEEK STRATO 10 AWG



TE Part #1051150-1
2007 7941 00,SMA RA CABLE PLUG



TE Part #1057159-1
3004 7941 00




TE Part #024278-000
D-181-3222-90/9



TE Part #109858-000
D-181-1222-90/9




TE Part #318821-000
SO96-3-01-100



TE Part #216121-006
55A0111-16-2



TE Part #2560-218-2031
CONT PIN



TE Part #ZPF00000000017891
FAST-E 03 M-X-B 00 B

Documents

Product Drawings

[D-181-2222-90/9](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_B-155_B-02X_B-04X](#)

English

[Raychem Electrical Interconnect Products](#)

English

Product Specifications

[Installation Procedure and Inspection Criteria for SolderSleeve Coaxial Cable Terminators on Coaxial Cables Rated for at Least 125 deg. C](#)

English