

EXTERNAL DESKTOP POWER SUPPLY 15VDC 50WATT



STONTRONICS: SW4323B

Features:

- Universal Input
- IEC-320-C14 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,GS,PSE,BSMI,CB



Description:

The TT Range of 50 Watt AC/DC switch mode power supplies provide 50 Watts of continuous output power in a high quality compact enclosure suitable for many general power applications.

Specification	
Part Number	SW4323B
Input Voltage Range	100 → 240 Vac
Input Frequency Range	50 → 60 Hz
Input Connector	IEC 320-C14
Input Current Rated	1.2A Max.
Inrush Current	70A Max. / 230Vac (Cold start at 25°C, full load)
Efficiency	88% Min
Input Power (Output: No Load)	<0.21W
Output Voltage Rating	15.0V
Output Current	3.34A Max.
Output Min Current	0A
Output Connection Type	2.1 x 5.5 x 12 mm Centre Positive – straight
Line and Load Regulation	+/-5%
Over Voltage Protection	V out 180% Max.
Over Load Protection	I out 180% Max.
Short Circuit Protection	Automatic recovery after short circuit fault being removed
Ripple Voltage	150mV Max
Hi-Pot	3000Vac 10mA 1 min
Safety Approved	UL / CUL / GS / PSE / BSMI / CB
EMI Standard	CE / FCC Class B ; Conduction & Radiation Met.
Operating Temperature Range	0°C → +40°C
Storage Temperature	-10°C → +80°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Dimensions	115(L) x 53(W) x 38(H)
MTBF	300,000Hrs.
Product Weight	258 g
Regulator Type	Switched Mode Power Supply

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

STONTRONICS

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500


EXTERNAL DESKTOP POWER SUPPLY

15VDC 50WATT

STONTRONICS: SW4323B



Diagrams



General Note
TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.