

SITOP BAT8600 PB 380WH
 SITOP BAT8600 Pb battery module for UPS8600 DC 48 V/380 Wh
 energy storage: mainten.-free lead batteries



Charging current charging voltage	
Rated voltage V_{out} DC	48 V
Rated current value I_{out} rated	20 A

Safety	
Short-circuit protection	blade-type fuse 40 A, 58 V DC
Design of the overload protection	Valve control

Safety	
Protection class	Class III
CE mark	Yes
UL/cUL (CSA) approval	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	IECEx Ex nA IIC T5 Gc; ATEX (EX) II 3G Ex nA IIC T5 Gc
Marine approval	DNV GL and ABS in process
Degree of protection (EN 60529)	IP20

Operating data note	
Operating data note	For storage, mounting and operation of batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed.

Ambient temperature	
<ul style="list-style-type: none"> during operation during transport during storage 	<p>-10 ... +50 °C</p> <p>-40 ... +60 °C</p> <p>-15 ... +40 °C</p>

Service life

Service life of energy storage	
<ul style="list-style-type: none"> typical Note at 20 °C typical at 30 °C typical at 40 °C typical at 50 °C typical 	<p>capacity falls to 80 % of original capacity (according to EUROBAT)</p> <p>4 y</p> <p>2 y</p> <p>1 y</p> <p>0.5 y</p>

Mechanics

Connection technology	Plug-in terminals with screw connectors
Connection for power supply unit	+, -: 2 plug-in terminals with 1 screwed connection each for 0.2 ... 10 mm ²
Product component belonging to	2x blade-type fuse 40 A, 58 V DC
Width of the enclosure	322 mm
Height of the enclosure	187 mm
Depth of the enclosure	110 mm
Installation width	322 mm
Installation height	207 mm
Weight, approx.	13 kg
Installation	keyhole mounting for hooking in to M4 screws
Reference identifier acc. to DIN EN 81346-2	G
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)