

Test pumps HP 500, 0 to 200 bar

With 30-L oval container or 60-L rectangular container



Application:

For hydrostatic testing of parts such as fittings, pipes, pipelines, tanks, gas bottles, test stands and many other high-pressure components.

Version:

- Test media: clear water, water/oil emulsion, hydraulic oil or low viscosity oil
- With drain valve, pressure gauge and hot-dip galvanised container

Advantage:

- 2-stage pumps with large piston for rapid filling of the system being tested and small piston for building the test pressure



Art. no.	56377 010
Model	HP 500
Container capacity	30 l
Min./max. pressure	2-200 bar
Design	Stationary
Connection thread	G 3/8 inch
Form	Oval
Feed volume per stroke	79 cm ³
Length x width x height	430 x 310 x 330 mm
Material	Sheet steel
Weight	18 kg