

Uncoated paper  
digital printing  
Copier/Printer  
Inkjet  
Duplex  
Offset/Preprint

# Océ | WOP611 Canon Océ Yellow Label Paper, 80 g/m<sup>2</sup>

## Product Information

### Product description

Canon Océ Yellow Label Paper is made using modern filler and fibre technology. This ensures a homogeneous composition and excellent print quality even at higher speeds.

### Physical Properties

<b>Weight</b>	80 g/m <sup>2</sup>	ISO 536	<b>Stiffness MD/CD</b>	130/55 mN	ISO 5628
<b>Calliper</b>	103 um	ISO 534	<b>Porosity</b>	730 ml/min	Bendtsen ISO 5636
<b>Whiteness</b>	147	CIE	<b>Roughness WS/TS</b>	210/210 ml/min	Bendtsen ISO 8791
<b>Opacity</b>	92 %	Elrepho			
<b>Acidity</b>	7.5	pH			

### Applications/Features

Yellow Label Paper produces high quality print in all applications, including house style, letter paper, pre-printed forms, copying, printing, inkjet and fax use.

### Available sizes

	A4	A3
<b>Grain direction</b>	LG	SG

LG = Longgrain, SG = Shortgrain

### Storage conditions

Temperature 10 – 30 °C, Relative Humidity 20 - 70%  
Repack opened reams or boxes when not in use.

### Print conditions

Acclimatize paper 24 hours before printing in printroom conditions (preferably next to printer)  
Best results are obtained between 15-25 °C and 30-65% RH (relative humidity)

### Environment, Health & Safety

ECF

EU Ecolabel



Emas



Nordic Swan certified



ISO 9001 and 14001 certified production site.

No Material Safety Data Sheet required.

Paper waste is suitable for recycling in most countries. Please refer to local paper recycle station.

### Processing guidelines, Tips & tricks

No special runnability advice.