

Kvalitet / Quality / Qualität:

861

Vægt / Weight / Gewicht	g/m²	230	EN 12127
Komposition / Composition / Gewebemischung	%	95/5 co/ ea	
Type/ Type/ Typ	Pique		

FARVEÆGTHEDER / COLOUR FASTNESS / FARBECHTHEIT

LIGHT COLOURS

Vaskeægted afsmiitning / Fastness to washing staining / Waschechtheit Anbluten	Note		ISO 105-C06
Svedægted afsmiitning/ Fastness to perspiration staining/ Schweißechtheit Anbluten	Note		ISO 105-E04
Gnidægted, våd / Fastness to rubbing, wet / Reibechtheit, nass	Note		ISO 105-X12
Gnidægted, tør / Fastness to rubbing, dry / Reibechtheit, trocken	Note		ISO 105-X12

FARVEÆGTHEDER / COLOUR FASTNESS / FARBECHTHEIT

DARK COLOURS

Vaskeægted afsmiitning / Fastness to washing staining / Waschechtheit Anbluten	Note	4-5	ISO 105-C06
Svedægted afsmiitning/ Fastness to perspiration staining/ Schweißechtheit Anbluten	Note	4-5	ISO 105-E04
Gnidægted, våd / Fastness to rubbing, wet / Reibechtheit, nass	Note	3	ISO 105-X12
Gnidægted, tør / Fastness to rubbing, dry / Reibechtheit, trocken	Note	4-5	ISO 105-X12

GENERELLE EGENSKABER / CHARACTERISTICS IN GENERAL / ALLGEMEINE EIGENSCHAFTEN

Dimensionsstabilitet / Dimensional stability / Dimensionsstabilität	%	+/-1,5	ISO 6330
Dimensionsstabilitet / Dimensional stability / Dimensionsstabilität	%		ISO 15797
Sømdrejning/ Spirality/ Verziehen	%	1,0	ISO 6330
Pilling : Martindale	note	4-5	ISO 12945-2

Certifikater / Certificates / Zertifikate	Oekotex 100, cl. II	
---	---------------------	---

Vaskesymboler/ Carelabel/ Pflegesymbole	
---	--

Bemærkninger / Remarks / Bemerkungen:	
---------------------------------------	--