


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6604: NEW LOGO'S, ADD PANTONE 400C	3/11/13	D.FRISIELLO
F	ECN 7231: REVISED DESCRIPTION FOR "HOOD"; NEW FORMAT, ROHS NOTE	1/9/14	D.FRISIELLO



WIRING MAP		
"J1"	WIRE COLOR	"J2"
1 & 6	BLACK	4
2	GRAY	3
3	RED	2
4	GREEN	1 & 6
5	BROWN	5
7	ORANGE	8
8	YELLOW	7
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CNULL9FF-5A	5.0	1.52
CNULL9FF-10A	10.0	3.05
CNULL9FF-25A	25.0	7.62

**NOTES:**

- PIN 9 NOT USED.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY MCCORMICK	6/27/2002		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY DOUG PARHAM	6/27/2002	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY R.CARRICK	6/27/2002	CABLE, DB9F/DB9F NULL MODEM	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
CSNULL-FS01	SCALE: NONE	CAD FILE: CSNULL9FF-A.SLDDRW	DWG. NO. CSNULL9FF-A	REV. <b>F</b>
			SHEET 1 OF 1	