

Bandsaw blades, welded, bi-metal, bulk stock, type UNI MAX 0° M42

Universal use -1300 N/mm² small cross-sections in profile and solid material



Application

Cutting of short-chipping solid material and profiles with small cross-sections in steel, stainless steel, cast iron and non-ferrous metals.

Advantage

- Stable 0° geometry optimised for small cross-sections and profiles
- Universal use in full cuts and interrupted cuts



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	80	40	25	20	20			65	65	40	40			60					

Art. No.	14044 055
Length	2375 mm
Width	20 mm
Thickness	0.9 mm
Type	UNI MAX 0°
Min./max. contact length of full material	3-8 mm
Number of teeth per inch	10/14
Min./max. contact length of profiles	1.5-4 mm

EAN-Code

4050293381887