

## FEATURES

- Can test multiple cables
- Included toner probe helps with testing
- Locate and identify the distance of an open or short circuit
- Measure the length of a cable with TDR
- Easy to read LCD backlit display

## RS PRO Network Cable Tester Network Tester F, RJ12, RJ45, 2670

RS Stock No.: 146-6833



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Introducing the RS PRO network cable tester with LAN cable tracer probe, a high performance tester kit ideal for troubleshooting and testing multiple cables such as UTP, STP, Cat cable and coaxial. The cable tester features a user friendly interface with an easy to read LCD backlit display, allowing you to view results quickly and efficiently. The LAN cable tracer probe is designed to identify and trace wires or cables within a group without damaging the insulation and can be used with any tone generator to identify wires.

## General Specifications

<b>Model Number</b>	2670
<b>Equipment Type</b>	Network Tester
<b>Connector Type</b>	RJ45, RJ12 (RJ11) & F connector
<b>Tone</b>	Yes
<b>Display type</b>	(Cable Tester): LCD Module (64mm x 33mm) (Probe): LED Indicator
<b>Applications</b>	UTP, STP, Cat5, Cat6, Coaxial

## Electrical Specifications

<b>Power Source</b>	9V dc Battery
<b>Battery Type</b>	Alkaline

## Mechanical Specifications

<b>Dimensions</b>	(Cable Tester): 195mm (L), 90mm (W), 40mm (H) (Probe): 230mm (L), 60mm (W), 28mm (H)
<b>Length</b>	195 mm
<b>Width</b>	90 mm
<b>Height</b>	40 mm

## Operation Environment Specifications

<b>Operating Temperature Range</b>	0°C to 50°C (32°F to 122°F)
<b>Storage Temperature Range</b>	-10°C - 60°C (14°F to 140°F)

## Approvals

<b>Compliance/Certifications</b>	CE, RoHS
----------------------------------	----------



RS Article No.	Body type	Kind of Cable Tester	Conditions of Cable Tester	Display	Operating way	Battery type
146-6833	Plastic	LAN, TEL, COAX	PASS, OPEN, SHORT, CROSS, SPLIT.	Graphic LCD	Rubber Keypad	Alkaline 9VDC