MICROSCOPES & REFRACTOMETERS 2023 MICROSCOPES



Stereo zoom microscope KERN OZL-44



LAB LINE

The affordable and flexible stereo zoom microscope for laboratories, inspection authorities and quality controls

Features

STANDARD

- The products in the KERN OZL-44 series are stereo zoom microscopes, which will impress you with their easy handling, flexibility as well as their stability and economical price
- The LED reflected and transmitted illumination included as standard guarantees the very best illumination of your sample
- As well as excellent optical characteristics and their large working surface, these models offer the highest level of comfort in this class – ideal for training companies, workshops as well as assembly and repair workstations, e.g. in the electronics industry
- The zoom objective gives you continuous magnification of 7,5× – 36×
- The OZL-44 series is available as a binocular version. The eyepieces are fixed in the eyepiece tube, to stop them getting damaged or lost

- The pillar stand offers you the highest level of flexibility and the freedom to remove the microscope head and to integrate it into other modular systems, for example into a universal stand
- A large selection of eyepieces, external illumination units as well as auxiliary objectives are available as accessories
- A protective dust cover, eye cups, as well as multi-lingual user instructions are included in the scope of delivery
- Please find detailed information in the following model outfit list

Scope of application

 In vitro fertilisation, detection of parasites, zoology and botany, tissue preparation, section, quality control

Applications/Samples

 Samples with focus on three-dimesnional impression, zoom with variable magnification (depth, thickness), e.g. insects, seeds, circuit boards, components

Technical data

- Optical system: Greenough optics
- Brightness adjustable (separate)
- Tube 45° inclined
- Magnification ratio: 4,8:1
- Interpupillary distance 55 75 mm
- Diopter adjustment: Both-sided
- Overall dimensions W×D×H 330×235×380 mm
- Net weight approx. 5 kg

	-							
Ö	00		Ð	ð	Q	Q		
360°	BINO	TRINO	LED	IL	TL	ZOOM	230 V	1 DAY

Model		Standard configuration				
	Tube	Eyepiece	Field of view	Objective	Stand	Illumination
KERN			mm	Zoom		
OZL 445	Binocular	WF 10×/Ø 20 mm	Ø 26.7 – 5.6	0.75×-3.6×	Pillar style	1 W LED (incident): 0.35 W LED (transmitted)

MICROSCOPES & REFRACTOMETERS 2023

MICROSCOPES

Stereo zoom microscope KERN OZL-44

OZL 445		S	pecifications - Obje	ctives			
Eyepiece	Magnification	Standard	Auxiliary objectives				
		1,0×	0,5×	0,75×	1,5×	2,0×	
WF 5×	Total magnification	3,75× - 18×	1,875×-9×	2,81×-13,5×	5,625×-27×	7,5×-36×	
	Field of view mm	Ø 26-6	Ø 60 – 13	Ø 32 – 7	Ø 16-4	Ø 12,5-3	
WF 10×	Total magnification	7,5×-36×	3,75×-18×	5,625×-27×	11,25×-54×	15×-72×	
	Field of view mm	Ø 26,7-5,6	Ø 53,3 – 11,1	Ø 35,5-7,4	Ø 17,8–3,7	Ø13,3-2,8	
WF 15×	Total magnification	11,25×-54×	5,625×-27×	8,44×-40,5×	16,875×-81×	22,5×-108×	
	Field of view mm	Ø 19-4,5	Ø 43-9,5	Ø 24 – 5,5	Ø 12-3	Ø 9,5 – 2	
WF 20×	Total magnification	15×-72×	7,5×-36×	56,25×-54×	22,5× - 108×	30×-144×	
	Field of view mm	Ø 12,5-3	Ø 28-6	Ø 16-3,5	Ø 8-2	Ø 6 – 1,5	
Working distan	ce	86 mm	178 mm	96 mm	42,5 mm	25,5 mm	
Maximum sample height		100 mm	10 mm	60 mm	120 mm	135 mm	

Model outfit		Model KERN	Order number
		OZL 445	
	WF 5×/Ø 16,2 mm	00	OZB-A4101
	WF 10×/Ø 20 mm	44	OZB-A4102
Eyepieces (30,5 mm)	WF 15×/Ø 15 mm	00	OZB-A4103
(,)	WF 20×/Ø 10 mm	00	OZB-A4104
	WF 10×/Ø 20 mm (reticule 0,1 mm)	0	OZB-A4151
	0,5×	0	OZB-A4201
	0,75×	0	OZB-A4202
Auxiliary objectives	1,5×	0	OZB-A4204
	2,0×	0	OZB-A4205
	Soldering protection lens	0	OZB-A4251
Stand	Pillar style, with LED illumination (0,35 W transmitted + 1 W incident)	✓	
Stage plate	Frosted glass/Ø 95 mm	√	OZB-A4805
	Black-white / Ø 95 mm	√	OZB-A4806
External illumination	Please find the information about external illumination	units in the catalogue on page 83 and on	the internet

 \checkmark = Included with delivery

O = Option

KERN

MICROSCOPES & REFRACTOMETERS 2023

KERN PICTOGRAMS



360° rotatable microscope head



Monocular Microscope For the inspection with one eye



Binocular Microscope For the inspection with both eyes



Trinocular Microscope For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser With high numerical aperture for the concentration and the focusing of light



Ð

LED

Halogen illumination For pictures bright and rich in contrast

LED illumination Cold, energy-saving and especially long-life illumination



Incident illumination For non-transparent objects



Transmitting illumination For transparent objects



Fluorescence illumination For stereomicroscopes

Fluorescence illumination for compound microscopes With 100 W mercury lamp and filter



Fluorescence illumination for compound microscopes With 3W LED illumination and filter



Phase contrast unit For a higher contrast



Darkfield condenser/unit For a higher contrast due to indirect illumination



To polarise the light











 ∞

INFINITY

Zoom magnification For stereomicroscopes

Infinity corrected optical system

Infinity system

Auto-focus





Parallel optical system For stereomicroscopes, enables fatigue-proof working

For automatic control of the focus level



SD card For data storage



USB 2.0 digital camera For direct transmitting of the picture to a PC USB 2.0



USB 3.0 digital camera For direct transmitting of the picture to a PC



WIFI data interface: For transmitting of the picture to a mobile display device



HDMI digital camera For direct transmitting of the picture to a display device



PC software To transfer the measurements from the device to a PC.



Automatic temperature compesation For measurements between 10 $^\circ\mathrm{C}$ and 30 $^\circ\mathrm{C}$



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013



C-Mount	Adapter for the connection of a camera to a trinocular microscope
FPS	Frames per second
H(S)WF	High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)
LWD	Long Working Distance
N.A.	Numerical Aperture
SLR camera	Single-Lens Reflex camera
SWF	Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)
W.D.	Working Distance
WF	Wide Field (Field number up to Ø22 mm for 10× eyepiece)
	······ ·······························



operation

Battery operation Ready for battery operation. The battery type is specified for each device.



Battery operation rechargeable Prepared for a rechargeable battery

230 V

Plug-in power supply 230V/50Hz in standard version for EU. On request GB, AUS or USA version.



Integrated power supply unit Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment The time required to manufacture the product internally is shown in days in the pictogram.