

Solid carbide end mill

2-cutter, uncoated



Application

For milling, recessing and contour milling of non-ferrous metals and plastics.

Version

- Solid carbide ultra-fine grain
- Straight shank in line with DIN 6535 HB
- With edge protection chamfer
- Defined edge rounding of the cutting edge
- Centre cutting
- Clearance
- Uncoated
- Mirror finish

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
						180	380	170	225	160	190	315							

Art. no.	16652 670
Cutting material	VHM
Surface	Uncoated
Type	W
Number of cutting edges	2 PCS
Twist angle	45°
Tool holding device	HB parallel shank
Overall length	Normal
Cutting edge diameter	3 mm
Cutting edge length	8 mm
Clearance length	18 mm
Length	57 mm
Edge protection chamfer length	0.1 mm
Clearance diameter	2.9 mm
Shaft diameter	6 mm
fz aluminium	0.013 mm
Overall stainless steel suitability	3
fitness not iron total	1
fitness Titan/Nickel/Super total	3

EAN-Code

4050293648317