

## SVJC boring bar, offset, HSS positive, right-hand

For face and longitudinal turning with CC indexable insert

**ATORN**<sup>®</sup>

### Application


For face and longitudinal turning with CC indexable insert 80°.

### Version

- Precision-made boring bar, **HSS**, with internal cooling, offset, type C, attack angle 95°, tip angle 80°, clearance angle 7°

### Advantage

- Universal use for face and longitudinal turning
- Positive body geometry ensures low cutting forces
- Very high rigidity and very good cut quality due to HSS base material



<b>Art. No.</b>	<b>17846 190</b>
<b>ISO name</b>	AH 1216 M SCLC R/L 06
<b>Min. bore diameter</b>	18 mm
<b>Tapered diameter</b>	12 mm
<b>Shaft diameter</b>	16 mm
<b>Clearance length</b>	50 mm
<b>Length</b>	150 mm
<b>Clamping surface height</b>	15 mm
<b>Programming size</b>	9 mm
<b>Suitable for indexable inserts</b>	CC.. 06..
<b>Tool design</b>	Right
<b>DIN</b>	8024

### EAN-Code

4050293111118