

## SVJC boring bar, offset, HSS positive, left-hand

For face and longitudinal turning with CC indexable insert

**ATORN**<sup>®</sup>

### Application


For face and longitudinal turning with CC indexable insert 80°.

### Version

- precision-manufactured **HSS** boring bar, with inner cooling, offset, C type, 95° pitch angle, 80° tip angle, 7° clearance angle

### Advantage

- Universal use for face and longitudinal turning
- Positive body geometry ensures low cutting forces
- Very high rigidity and very good cut quality due to HSS base material



<b>Art. No.</b>	<b>17846 194</b>
<b>ISO name</b>	AH 0810 J SCLC R/L 06
<b>Min. bore diameter</b>	12 mm
<b>Tapered diameter</b>	8 mm
<b>Shaft diameter</b>	10 mm
<b>Clearance length</b>	32 mm
<b>Length</b>	110 mm
<b>Clamping surface height</b>	9 mm
<b>Programming size</b>	6 mm
<b>Suitable for indexable inserts</b>	CC.. 06..
<b>Tool design</b>	Left
<b>DIN</b>	8024

### EAN-Code

4050293111040