

STURTEVANT RICHMONT signal torque wrench



Application:

For the most demanding requirements around torque precision in series production, for replaceable plug-in tools no. 52250-52256.



Execution:

- Automatic, audible and perceptible release when the tightening torque is reached
- Can be adjusted using a special wrench and a torque tester or measuring wrench (not included in delivery)

Art. no.	52249 250
Brand	SR STURTEVANT RICHMONT
Manufacturer Part Number	R8 10014
Min. torque	40 Nm
Max. torque	200 Nm
Min./max. torque	40-200 Nm
With scale	No
Adapter type	Dove tail
Length	405 mm
Error limit (%)	4 %
Gross Weight	0.801 kg
Product Group	536

EAN

4260667410116