

## SB 23 Plus MK2 pillar drill

Power supply 400 V

### Application:

Universal drill with continuously variable speed drive, precision depth stop adjustment, connecting cable and CEE plug.

### Version:

- Finely adjustable drill depth stop
- Emergency stop palm button
- Infinitely variable speed control
- Drilling machine protection with electr. protection
- Digital rotation speed and drilling depth display
- LED lighting
- Thread cutting device

<b>Art. no.</b>	<b>79130 170</b>
<b>Model</b>	SB 23 Plus MK2
<b>Max. drill diameter in steel E335/St 60 (continuous mode)</b>	23 mm
<b>Max. drill diameter in steel E335/St 60 (normal mode)</b>	25 mm
<b>Max. thread-cutting performance</b>	M16
<b>Drill chuck holder</b>	MT 2
<b>Spindle stroke</b>	100 mm
<b>Overhang</b>	260 mm
<b>Pillar diameter</b>	82 mm
<b>Clamping area</b>	340 x 420 mm
<b>T-slots on clamping table (number x width x spacing)</b>	2 x 13/26 x 125
<b>Feed type</b>	Manual
<b>Number of drive levels</b>	Continuous
<b>Weight</b>	165 kg
<b>Total engine capacity</b>	1.5/1.5 kW
<b>Min./max. spindle speed</b>	20-2000 rpm



### EAN-Code

4251762500406