

T-1 3/4 (5mm) BI-COLOR INDICATOR LAMP

Part Number: L-59SURKCGKW

Hyper Red Green


Features

- Uniform light output.
- Low power consumption.
- 3 leads with one common lead.
- Long life-solid state reliability.
- RoHS compliant.

Descriptions

- The Hyper Red source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode.
- The Green source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode.

Package Dimensions



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.25(0.01") unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.4. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

SPEC NO: DSAB8533 **REV NO: V.20A** DATE: JUL/03/2015 PAGE: 1 OF 7 **APPROVED: Wynec CHECKED: Allen Liu** DRAWN: M.Liu ERP: 1101005941

Selection Guide

Part No.	Emitting Color (Material)	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
L-59SURKCGKW	Hyper Red (AlGaInP)	White Diffused	600	1200	- 60°
			*80	*200	
	Green (AlGaInP)		80	180	
			*80	*180	

Notes:

- 1. θ 1 / 2 is the angle from optical centerline where the luminous intensity is 1 / 2 of the optical peak value.
- 2. Luminous intensity/ luminous Flux: + / -15%.

 * Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Emitting Color	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Hyper Red Green	645 574		nm	IF=20mA
λD [1]	Dominant Wavelength	Hyper Red Green	630 570		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Hyper Red Green	28 20		nm	IF=20mA
С	Capacitance	Hyper Red Green	35 15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Hyper Red Green	1.95 2.1	2.5 2.5	V	IF=20mA
lr	Reverse Current	Hyper Red Green		10 10	uA	V _R = 5V

- 1.Wavelength: + / -1nm.
 2.Forward Voltage: + / -0.1V.
 3.Wavelength value is traceable to the CIE127-2007 compliant national standards.
- 4. Excess driving current and/or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.


Absolute Maximum Ratings at TA=25°C

Parameter	Hyper Red	Red Green			
Power dissipation	75	75	mW		
DC Forward Current	30	30	mA		
Peak Forward Current [1]	185	150	mA		
Reverse Voltage		V			
Operating / Storage Temperature	-40°C To +85°C				
Lead Solder Temperature [2]	260°C For 3 Seconds				
Lead Solder Temperature [3]	260°C For 5 Seconds				


Notes:


- 1. 1 / 10 Duty Cycle, 0.1ms Pulse Width.
 2. 2mm below package base.
- 3. 5mm below package base.


SPEC NO: DSAB8533 **REV NO: V.20A** DATE: JUL/03/2015 PAGE: 2 OF 7 **APPROVED: Wynec CHECKED: Allen Liu** DRAWN: M.Liu ERP: 1101005941





L-59SURKCGKW Hyper Red














 SPEC NO: DSAB8533
 REV NO: V.20A
 DATE: JUL/03/2015
 PAGE: 3 OF 7


 APPROVED: Wynec
 CHECKED: Allen Liu
 DRAWN: M.Liu
 ERP: 1101005941

Green















SPATIAL DISTRIBUTION

SPEC NO: DSAB8533 REV NO: V.20A DATE: JUL/03/2015 PAGE: 4 OF 7
APPROVED: Wynec CHECKED: Allen Liu DRAWN: M.Liu ERP: 1101005941



Terms and conditions for the usage of this document


- 1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- 5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6. All design applications should refer to Kingbright application notes available at http://www.kingbright.com/application notes

 SPEC NO: DSAB8533
 REV NO: V.20A
 DATE: JUL/03/2015
 PAGE: 5 OF 7

 APPROVED: Wynec
 CHECKED: Allen Liu
 DRAWN: M.Liu
 ERP: 1101005941

PRECAUTIONS


- 1. Storage conditions:
 - a. Avoid continued exposure to the condensing moisture environment and keep the product away from rapid transitions in ambient temperature.
 - b.LEDs should be stored with temperature ≤30°C and relative humidity < 60%.
 - c.Product in the original sealed package is recommended to be assembled within 72 hours of opening. Product in opened package for more than a week should be baked for 30 (\pm 10/-0) hours at 85 ~ 100°C.
- 2. The lead pitch of the LED must match the pitch of the mounting holes on the PCB during component placement. Lead-forming may be required to insure the lead pitch matches the hole pitch. Refer to the figure below for proper lead forming procedures. (Fig. 1)



"O" Correct mounting method "X" Incorrect mounting method

Note 1-3: Do not route PCB trace in the contact area between the leadframe and the PCB to prevent short-circuits.

3. When soldering wires to the LED, each wire joint should be separately insulated with heat-shrink tube to prevent short-circuit contact. Do not bundle both wires in one heat shrink tube to avoid pinching the LED leads. Pinching stress on the LED leads may damage the internal structures and cause failure. (Fig. 2)




4. Use stand-offs (Fig.3) or spacers (Fig.4) to securely position the LED above the PCB.




- 5. Maintain a minimum of 3mm clearance between the base of the LED lens and the first lead bend. (Fig. 5 and 6)
- During lead forming, use tools or jigs to hold the leads securely so that the bending force will not be transmitted
 to the LED lens and its internal structures. Do not perform lead forming once the component has been
 mounted onto the PCB. (Fig. 7)

SPEC NO: DSAB8533 REV NO: V.20A DATE: JUL/03/2015 PAGE: 6 OF 7
APPROVED: Wynec CHECKED: Allen Liu DRAWN: M.Liu ERP: 1101005941


7. Do not bend the leads more than twice. (Fig. 8)



8. During soldering, component covers and holders should leave clearance to avoid placing damaging stress on the LED during soldering.



- 9. The tip of the soldering iron should never touch the lens epoxy.
- 10. Through-hole LEDs are incompatible with reflow soldering.
- 11. If the LED will undergo multiple soldering passes or face other processes where the part may be subjected to intense heat, please check with Kingbright for compatibility.
- 12. Recommended Wave Soldering Profiles:



Notes:

- 1.Recommend pre-heat temperature of 105°C or less (as measured with a thermocouple attached to the LED pins) prior to immersion in the solder wave with a maximum solder bath temperature of 260°C
- 2.Peak wave soldering temperature between 245° C ~ 255° C for 3 sec (5 sec max).
- 3.Do not apply stress to the epoxy resin while the temperature is above 85°C.
- 4. Fixtures should not incur stress on the component when mounting and during soldering process.
- 5.SAC 305 solder alloy is recommended.
- 6.No more than one wave soldering pass.

 SPEC NO: DSAB8533
 REV NO: V.20A
 DATE: JUL/03/2015
 PAGE: 7 OF 7

 APPROVED: Wynec
 CHECKED: Allen Liu
 DRAWN: M.Liu
 ERP: 1101005941