



**Part Number :** [464373132](#)


**Product Description :** EXTreme Ten60Power Right-Angle Plug with Side Guides, 35 Signal Circuits, Press Fit Tail

**Series Number :** 46437

**Status :** Active

**Product Category :** Board-to-Board Connectors

**Engineering Number :** 046437-3132



---

## Documents & Resources

### Drawings

[Drawing 464373132\\_sd.pdf](#)

[Packaging Design Drawing 464371001-PK-000.pdf](#)

[Packaging Design Drawing PK-46437-001-000.pdf](#)

[Packaging Design Drawing PK-46437-005-001.pdf](#)

### 3D Models and Design Files

[3D Model 464373132\\_stp.zip](#)

### Specifications


[Product Specification PS-46436-100-001.pdf](#)

[Test Summary 464361000-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Board-to-Board Connectors
Series	46437
Description	EXTreme Ten60Power Right-Angle Plug with Side Guides, 35 Signal Circuits, Press Fit Tail
Application	Board-to-Board, Signal
Comments	See Product Specification for details
Component Type	PCB Header
Product Family	EXTreme Ten60 High-Power Connectors
Product Name	EXTreme Ten60Power
UPC	193264257157

#### Agency

CSA	LR19980
UL	E29179

#### Electrical

Current - Maximum per Contact	4.5A
Voltage - Maximum	120V

#### Physical

Breakaway	No
Circuits (Loaded)	35
Circuits (maximum)	35
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	No
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	8.113/g
Number of Rows	5
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	2.50mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	0p - 35s
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole - Compliant Pin

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
EXTreme Ten60Power Right-Angle Receptacle with Side Guides, 35 Signal Circuits, Press Fit Tail	<u>0464363132</u>
EXTreme Ten60Power Vertical Receptacle with Side Guides, 35 Signal Circuits, Press Fit Tail	<u>0465623132</u>

---

This document was generated on Sep 26, 2023