


E11250



Connecting cable with socket

ADOGA050MSS0005H04



Application

Special feature

Halogen-free

Electrical data

Operating voltage

[V]

< 300 AC

Operating conditions

Ambient temperature

[°C]

-25...90

Protection

IP 67

Mechanical data

Weight

[g]

163.6

Dimensions

[mm]

14.5 x 14.5 x 42.5

Materials

TPU

Material nut

brass, nickel-plated

Remarks

Pack quantity


1 pcs.

Electrical connection

Cable: 5 m, PUR, Halogen-free, black, Ø 4.7 mm; 4 x 0.34 mm² (43 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x 1/2", straight; Moulded body: TPU; Locking: brass, nickel-plated




E11250



Connecting cable with socket

ADOGA050MSS0005H04

Connection



Core colours :

BK =	black
BN =	brown
BU =	blue
WH =	white