



Part no.: 547935  
**MSI-DT30B-01**  
Safety relay



Figure can vary

## Contents

- Technical data
- Electrical connection
- Operation and display

Part no.: 547935 – MSI-DT30B-01 – Safety relay

## Technical data

<b>Basic data</b>	
Series	MSI-DT
<b>Functions</b>	
Functions	Cross circuit monitoring One- or two-channel operation Start/restart interlock (RES), selectable Time-delayed shutdown (STOP1)
Restart	Automatic Manual
<b>Characteristic parameters</b>	
SIL	3 , IEC 61508
SILCL	3 , IEC/EN 62061
Performance Level (PL)	e , EN ISO 13849-1
MTTF <sub>d</sub>	124 years , EN ISO 13849-1
PFH <sub>D</sub>	0.000000018 per hour
PFH <sub>D</sub>	1,8E-09 per hour
Mission time T <sub>M</sub>	20 years , EN ISO 13849-1
Category	4 , EN ISO 13849
STOP category	0 , IEC/EN 60204-1
B10 <sub>d</sub> at DC13 (inductive load)	400,000 number of cycles
B10 <sub>d</sub> at AC15 (inductive load)	400,000 number of cycles
<b>Electrical data</b>	
Protective circuit	Short circuit protected
<b>Control circuit</b>	
Executing the switching function of the inputs	Changeover
Nominal output voltage DC	24 V
Voltage permitted at the input	30 V
Test pulse time permitted t <sub>TP</sub>	1 ms
Release time t <sub>R</sub> , time-delayed contacts (tolerance)	0.1 s ... 30 s ± 40 %
<b>Connection</b>	
Number of connections	1 Piece(s)
<b>Connection 1</b>	
Type of connection	Terminal
Function	Connection to device Voltage supply
Type of terminal	Screw terminal
No. of pins	16 -pin
<b>Cable properties</b>	
Connection cross sections	1 x 0.2 to 2.5 mm <sup>2</sup> , wire 1 x 0.2 to 2.5 mm <sup>2</sup> , wire
<b>Mechanical data</b>	
Dimension (W x H x L)	22.5 mm x 99 mm x 114.5 mm
Housing material	Plastic , Unreinforced polyamide PA
Net weight	231 g

## Part no.: 547935 – MSI-DT30B-01 – Safety relay

Housing color	Gray
Type of fastening	Snap-on mounting
Mechanical life time	100,000,000 actuation cycles

### Operation and display

Type of display	LED
Number of LEDs	3 Piece(s)

### Environmental data

Ambient temperature, operation	-20 ... 55 °C
Ambient temperature, storage	-40 ... 70 °C

### Certifications

Degree of protection	IP 20 (terminals) IP 40 (housing)
Certifications	c UL US TÜV Rheinland

### Classification

Customs tariff number	85371098
eCl@ss 8.0	27371819
eCl@ss 9.0	27371819
ETIM 5.0	EC001449
ETIM 6.0	EC001449

## Electrical connection

Connection 1	
Type of connection	Terminal
Function	Connection to device Voltage supply
Type of terminal	Screw terminal
No. of pins	16 -pin

Terminal	Assignment
A1	+24V
S35	Start circuit
S34	Start circuit
A2	GND
S11	Sensor input 1
S12	Sensor input 1
S21	Sensor input 2
S22	Sensor input 2
13	1 release circuit, undelayed
14	1 release circuit, undelayed
23	2 release circuit, undelayed
24	2 release circuit, undelayed
37	Release circuit 1, delayed
38	Release circuit 1, delayed

Terminal	Assignment
47	Release circuit 2, delayed
48	Release circuit 2, delayed

## Operation and display

### LEDs

Display LED 1	Display LED 2	Display LED 3	Meaning
Green, continuous light	Off	Off	Operational readiness
Green, continuous light	Green, continuous light	Green, continuous light	Device is active. Release circuits are closed.
Green, quickly flashing	Off	Off	Internal error - device defective. Replace the device!
Green, slowly flashing	Off	Off	External error - check the wiring and power supply! In event of manual reset: check the time sequence!
Green, slowly flashing	Green, slowly flashing	Off	Configuration error - repeat the configuration! If this cannot be performed: check the wiring and power supply!
Green, slowly flashing	Green, slowly flashing	Green, slowly flashing	Configuration necessary - positioner for delay time was readjusted. Configure again!