

Air compressor MEGA 700-90 D

metabo®

Version:

- For three-phase current
- Oil-lubricated 2-cylinder piston compressor for high air delivery
- Belt drive for low motor speeds and quiet running
- Instrument panel with easily legible manometers for tank and operating pressure
- Cord wrap facility
- Rubberised, robust wheels and handle for mobile applications
- Steering rollers with parking brake for good manoeuvrability
- Filter pressure reducer including manometer and mist lubricator for improved air quality and controllable working pressure
- After-cooler for reduced condensation

Advantage:

- Push button with starter valve for reliable cold start
- 10-year boiler warranty against rust penetration



| | |
|---------------------------------------------------------|----------------------|
| Art. no. | 75290 041 |
| Model | Mega 700-90 D |
| Operating pressure | 11 bar |
| Intake air capacity | 650 l/min |
| Delivery quantity effective at 80% max. pressure | 450 l/min |
| Filling capacity | 520 l/min |
| Tank capacity | 90 l |
| Power input | 4000 W |
| Max. rotation speed | 1400 rpm |
| Sound-pressure level | 88 dB |
| Length x width x height | 1188 x 520 x 1110 mm |
| Weight | 119 kg |
| With overload protection | Yes |

EAN-Code

4007430244833