



MASTER PL-L Xtra Polar 4 Pin

MASTER PL-L Xtra Polar 36W/830/4P 1CT

Energy saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of two parallel fluorescent tubes linked by a bridge

Product data

• Product Data

Order code	927907783015
Full product code	927907783015
Full product name	MASTER PL-L Xtra Polar 36W/830/4P 1CT
Order product name	MASTER PL-L Xtra Polar 36W/830/4P 1CT/25
Pieces per pack	1
Packing configuration	25
Packs per outerbox	25
Bar code on pack - EAN1	8711500267764
Bar code on outerbox - EAN3	8711500267771
Logistic code(s) - 12NC	927907783015
ILCOS code	FSD-36/30/1B-E-2G11
Net weight per piece	104.000 gr

• General Characteristics

System Description	-
Cap-Base	2G11
Cap-Base Information	4P
Life to 50% failures EM	21000 hr
Life to 50% fail Preheat EL,3h	36000 hr
Life to 50% fail Nonpreh EL,3h	11000 hr
Life to 10% fail Nonpreh EL,3h	7000 hr
Life to 10% fail Preheat EL,3h	25000 hr
Life to 10% failures EM	14000 hr

LSF HF Preheat 20000h Rated,3h	94 %
LSF HF Preheat 12000h Rated,3h	98 %
LSF HF Preheat 8000h Rated,3h	99 %
LSF HF Preheat 6000h Rated,3h	99 %
LSF HF Preheat 4000h Rated,3h	99 %
LSF HF Preheat 2000h Rated,3h	99 %
LSF EM 20000h Rated,3h cycle	58 %
LSF EM 16000h Rated,3h cycle	88 %
LSF EM 12000h Rated,3h cycle	95 %
LSF EM 8000h Rated,3h cycle	97 %
LSF EM 6000h Rated,3h cycle	98 %
LSF EM 4000h Rated,3h cycle	99 %
LSF EM 2000h Rated,3h cycle	99 %
LSF HF Preheat 16000h Rated,3h	97 %

• Electrical Characteristics

Lamp Wattage	36 W
Lamp Voltage EL 25°C	90 V
Lamp Current EL 25°C	0.360 A
Dimmable	Yes



asimpleswitch.com

PHILIPS

sense and simplicity

MASTER PL-L Xtra Polar 4 Pin

Lamp Current EM 25°C	0.445 A
Lamp Wattage EL 25°C, Rated	36.0 W
Lamp Wattage EL 25°C, Nominal	36 W
Lamp Voltage EM 25°C	102 V

• Environmental Characteristics

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content	3.0 mg

• Light Technical Characteristics

Color Code	830 [CCT of 3000K]
Color Rendering Index	82 Ra8
Color Designation (text)	Warm White
Color Temperature	3000 K
Chromaticity Coordinate X	440 -
Chromaticity Coordinate Y	405 -
LLMF EM 20000h Rated	88 %
LLMF EM 16000h Rated	89 %
LLMF EM 12000h Rated	90 %
LLMF EM 8000h Rated	91 %
LLMF EM 6000h Rated	92 %
LLMF EM 4000h Rated	93 %
LLMF EM 2000h Rated	94 %
LLMF HF 20000h Rated	90 %



LLMF HF 16000h Rated	90 %
LLMF HF 12000h Rated	91 %
LLMF HF 8000h Rated	92 %
LLMF HF 6000h Rated	93 %
LLMF HF 4000h Rated	94 %
LLMF HF 2000h Rated	95 %
Luminous Flux EL 25°C, Rated	2900 Lm
Luminous Flux EL 25°C, Nominal	2900 Lm
Lum Flux Rated HF 25°C,horiz	2900 Lm
Lum Flux Nominal HF 25°C,horiz	2900 Lm
Lum Efficacy Rated HF 25°C,hor	81 Lm/W
Design Temperature	18 C
Lum Efficacy Rated EM 25°C,hor	81 Lm/W
Lum Flux Nominal EM 25°C,horiz	2900 Lm
Lum Flux Rated EM 25°C,horiz	2900 Lm

• Product Dimensions

Base Face to Base Face A	384.2 mm
Insertion Length B	410 mm
Overall Length C	416.6 mm
Diameter D	37.7 mm
Diameter D1	18 mm



• Measuring Conditions

Dimensional drawing



Product	A (Max)	B (Max)	C (Max)	D (Max)	D1 (Max)
PL-L Xtra 36W/830/4P LT	384.2	410	416.6	37.7	18

Photometric data



Lamps being part of this product family comply with Commission Regulation (EC) No 245/2009 – Ecodesign requirements, applicable from 13 April 2010.

1.3 Product information requirements on lamps

- Nominal and rated lamp wattage;
- Nominal and rated lamp luminous flux;
- Rated lamp efficacy at 100 h in standard conditions (25 °C, for T5 lamps at 35 °C). For fluorescent lamps both at 50 Hz (mains frequency) operation (where applicable) and at High Frequency (> 50 Hz) operation (where applicable) for the same rated luminous flux in all cases, indicating for High Frequency operation the calibration current of the test conditions and/or the rated voltage of the HF generator with the resistance. It shall be stated in a conspicuous manner that the power dissipated by auxiliary equipment such as ballasts is not included in the power consumed by the source;
- Rated lamp Lumen Maintenance Factor at 2000 h, 4000 h, 6000 h, 8000 h, 12000 h, 16000 h and 20000 h (up to 8000 h only for new lamps on the market where no data is yet available), indicating which operation mode of the lamp was used for the test if both 50 Hz and High Frequency operation are possible;
- Rated lamp Survival Factor at 2000 h, 4000 h, 6000 h, 8000 h, 12000 h, 16000 h and 20000 h (up to 8000 h only for new lamps on the market where no data is yet available), indicating which operation mode of the lamp was used for the test if both 50 Hz and High Frequency operation are possible;
- Lamp mercury content as X.X mg;
- Colour Rendering Index (Ra) of the lamp;
- Colour temperature of the lamp;
- Ambient temperature inside the luminaire at which the lamp was designed to maximise its luminous flux. If this temperature is equal to or lower than 0 °C or equal to or higher than 50 °C it shall be stated that the lamp is not suitable for indoor use at standard room temperatures;
- For fluorescent lamps without integrated ballast, the energy efficiency index(es) of ballasts as defined in Table 17 with which the lamp can operate.
See Table 17-EuP245.pdf for Table 17 – Energy efficiency index requirements for non-dimmable ballasts for fluorescent lamps.
For more information see: <http://eur-lex.europa.eu/LexUriServ/LexUriServ.do?uri=OJ:L:2009:076:0017:0044:EN:PDF>



© 2011 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2011, January 16
data subject to change