



Figure similar

TRANSFORMER SITAS; PHASES:1;  
 PN/PN(S6)(KVA):1 /5; UPRI(V):400-230+/-15;  
 USEC(V):2X115; ISEC(A):4,35-8,70; F(HZ):50...60;  
 VECTOR GR./SHIELD WNG.:II0 /0; TA/ISOKL:40 /B;  
 IP00; TYPE OF TERMINALS:SCREW/TAB  
 CONNECTION; INSTALLATION:SCREW; EN 61558-2-  
 1, -2-2, -2-4 >UL/CSA-RECOGNIZED< >CONTROL  
 CIRCUIT TRANSFORMER< >ISOLATION  
 TRANSFORMER<

General technical data:

Product designation		transformer SITAS
product brand name		SIDAC
Operating apparent output Rated value	V·A	1 000
Efficiency		0.93
Connection method for transformers		II0
Certificate of suitability		CE / cRUus
Product function		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
Number of shielding windings		0
Short-term vector power	V·A	5 000
Relative short-circuit voltage	%	2.33

Inputs:

Phase number of the inputs		1
Input voltage		
• _1 Rated value	V	415
• _2 Rated value	V	400
• _3 Rated value	V	385
• _4 Rated value	V	245
• _5 Rated value	V	230
• _6 Rated value	V	215
Electrical input frequency		

- minimum
- maximum

Hz	50
Hz	60

#### Outputs:

<b>Phase number of the outputs</b>		1
<b>Output voltage</b>		
• _1 Rated value	V	230
• _2 Rated value	V	115
<b>Electrical output frequency</b>		
• maximum	Hz	60
• minimum	Hz	50

#### Ambient conditions:

<b>Thermal class acc. to IEC 60085</b>		B
<b>Ambient temperature Rated value</b>	°C	40
<b>Protection class IP</b>		IP00

#### Mechanical data:

<b>Type of electrical connection</b>		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals
<b>Mounting type</b>		screws
<b>Construction form of the iron core</b>		EI 150/90
<b>Width</b>	m	0.152
<b>Height</b>	m	0.144
<b>Depth</b>	m	0.132

#### Certificates/ approvals:

General Product Approval

Shipping Approval

other



[other](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM57428JD400FA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4AM57428JD400FA0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4AM57428JD400FA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM57428JD400FA0&lang=en)

last modified:

15.01.2015