



56 mm sq. (2.20 inch sq.)

1.8° /step **RoHS**

Unipolar winding, Lead wire type
Bipolar winding, Lead wire type▶ p. 70

Customizing

Hollow | Shaft modification
Decelerator | Encoder

Varies depending on the model number and quantity. Contact us for details.


Unipolar winding, Lead wire type

Model number		Holding torque at 2-phase energization	Rated current	Wiring resistance	Winding inductance	Rotor inertia	Mass (Weight)	Motor length (L)
Single shaft	Dual shaft	[N·m (oz-in) min.]	A/phase	Ω /phase	mH/phase	[×10 ⁻⁴ kg·m ² (oz·in ²)]	[kg (lbs)]	mm (in)
103H7121-0140	103H7121-0110	0.39 (55.2)	1	4.8	8	0.1 (0.55)	0.47 (1.04)	41.8 (1.65)
103H7121-0440	103H7121-0410	0.39 (55.2)	2	1.25	1.9	0.1 (0.55)	0.47 (1.04)	41.8 (1.65)
103H7121-0740	103H7121-0710	0.39 (55.2)	3	0.6	0.8	0.1 (0.55)	0.47 (1.04)	41.8 (1.65)
103H7123-0140	103H7123-0110	0.83 (117.5)	1	6.7	15	0.21 (1.15)	0.65 (1.43)	53.8 (2.12)
103H7123-0440	103H7123-0410	0.83 (117.5)	2	1.6	3.8	0.21 (1.15)	0.65 (1.43)	53.8 (2.12)
103H7123-0740	103H7123-0710	0.78 (110.5)	3	0.77	1.58	0.21 (1.15)	0.65 (1.43)	53.8 (2.12)
103H7124-0140	103H7124-0110	0.98 (138.8)	1	7	14.5	0.245 (1.34)	0.8 (1.76)	63.8 (2.51)
103H7124-0440	103H7124-0410	0.98 (138.8)	2	1.7	3.1	0.245 (1.34)	0.8 (1.76)	63.8 (2.51)
103H7124-0740	103H7124-0710	0.98 (138.8)	3	0.74	1.4	0.245 (1.34)	0.8 (1.76)	63.8 (2.51)
103H7126-0140	103H7126-0110	1.27 (179.8)	1	8.6	19	0.36 (1.97)	0.98 (2.16)	75.8 (2.98)
103H7126-0440	103H7126-0410	1.27 (179.8)	2	2	4.5	0.36 (1.97)	0.98 (2.16)	75.8 (2.98)
103H7126-0740	103H7126-0710	1.27 (179.8)	3	0.9	2.2	0.36 (1.97)	0.98 (2.16)	75.8 (2.98)

Characteristics diagram


103H7121-0140 103H7121-0110

Constant current circuit
Source voltage: 24 VDC
Operating current:
1 A/phase, 2-phase
energization (full-step)
 $J_c=[0.94 \times 10^{-4} \text{kg}\cdot\text{m}^2 (5.14 \text{ oz}\cdot\text{in}^2)]$ use the rubber
coupling]
fs: Maximum self-start
frequency when not
loaded




103H7121-0440 103H7121-0410

Constant current circuit
Source voltage: 24 VDC
Operating current:
2 A/phase, 2-phase
energization (full-step)
 $J_c=[0.94 \times 10^{-4} \text{kg}\cdot\text{m}^2 (5.14 \text{ oz}\cdot\text{in}^2)]$ use the rubber
coupling]
fs: Maximum self-start
frequency when not
loaded




103H7121-0740 103H7121-0710

Constant current circuit
Source voltage: 24 VDC
Operating current:
3 A/phase, 2-phase
energization (full-step)
 $J_c=[0.94 \times 10^{-4} \text{kg}\cdot\text{m}^2 (5.14 \text{ oz}\cdot\text{in}^2)]$ use the rubber
coupling]
fs: Maximum self-start
frequency when not
loaded




103H7123-0140 103H7123-0110

Constant current circuit
Source voltage: 24 VDC
Operating current:
1 A/phase, 2-phase
energization (full-step)
 $J_c=[0.94 \times 10^{-4} \text{kg}\cdot\text{m}^2 (5.14 \text{ oz}\cdot\text{in}^2)]$ use the rubber
coupling]
fs: Maximum self-start
frequency when not
loaded




103H7123-0440 103H7123-0410

Constant current circuit
Source voltage: 24 VDC
Operating current:
2 A/phase, 2-phase
energization (full-step)
 $J_c=[0.94 \times 10^{-4} \text{kg}\cdot\text{m}^2 (5.14 \text{ oz}\cdot\text{in}^2)]$ use the rubber
coupling]
fs: Maximum self-start
frequency when not
loaded



103H7123-0740 103H7123-0710


Constant current circuit
Source voltage: 24 VDC
Operating current:
3 A/phase, 2-phase
energization (full-step)
 $J_c=[0.94 \times 10^{-4} \text{kg}\cdot\text{m}^2 (5.14 \text{ oz}\cdot\text{in}^2)]$ use the rubber
coupling]
fs: Maximum self-start
frequency when not
loaded




Characteristics diagram

**103H7124-0140
103H7124-0110**


Constant current circuit
Source voltage: 24 VDC
Operating current:
1 A/phase, 2-phase
energization (full-step)
 $J_L = [2.6 \times 10^{-4} \text{kg}\cdot\text{m}^2 (14.22 \text{ oz}\cdot\text{in}^2)]$ use the rubber coupling
fs: Maximum self-start frequency when not loaded


**103H7124-0440
103H7124-0410**


Constant current circuit
Source voltage: 24 VDC
Operating current:
2 A/phase, 2-phase
energization (full-step)
 $J_L = [2.6 \times 10^{-4} \text{kg}\cdot\text{m}^2 (14.22 \text{ oz}\cdot\text{in}^2)]$ use the rubber coupling
fs: Maximum self-start frequency when not loaded


**103H7124-0740
103H7124-0710**


Constant current circuit
Source voltage: 24 VDC
Operating current:
3 A/phase, 2-phase
energization (full-step)
 $J_L = [2.6 \times 10^{-4} \text{kg}\cdot\text{m}^2 (14.22 \text{ oz}\cdot\text{in}^2)]$ use the rubber coupling
fs: Maximum self-start frequency when not loaded


**103H7126-0140
103H7126-0110**


Constant current circuit
Source voltage: 24 VDC
Operating current:
1 A/phase, 2-phase
energization (full-step)
 $J_L = [2.6 \times 10^{-4} \text{kg}\cdot\text{m}^2 (14.22 \text{ oz}\cdot\text{in}^2)]$ use the rubber coupling
fs: Maximum self-start frequency when not loaded


**103H7126-0440
103H7126-0410**

Constant current circuit
Source voltage: 24 VDC
Operating current:
2 A/phase, 2-phase
energization (full-step)
 $J_L = [2.6 \times 10^{-4} \text{kg}\cdot\text{m}^2 (14.22 \text{ oz}\cdot\text{in}^2)]$ use the rubber coupling
fs: Maximum self-start frequency when not loaded



**103H7126-0740
103H7126-0710**

Constant current circuit
Source voltage: 24 VDC
Operating current:
3 A/phase, 2-phase
energization (full-step)
 $J_L = [2.6 \times 10^{-4} \text{kg}\cdot\text{m}^2 (14.22 \text{ oz}\cdot\text{in}^2)]$ use the rubber coupling
fs: Maximum self-start frequency when not loaded




Dimensions [Unit: mm (inch)]

Lead wire: UL1430 (103H7121, 103H7124, 103H7126), AWG22
UL3266 (103H7123), AWG22



Internal wiring



Compatible drivers

- For motor model number 103H712 □ -01 □ 0 (1 A/phase),
103H712 □ -07 □ 0 (3 A/phase)
Driver is not included.
If you require assistance finding a driver, contact us for details.
 - For model number 103H712 □ -04 □ 0 (2 A/phase)
Model number: US1D200P10 (DC input)
Operating current select switch setting: 0
- The characteristics diagram shown above is from our experimental circuit.*

General Specifications

Motor model number	SH2141	SH228	SH353	SS242	SH142	103H52	SS250	103H67	103H712
Type	—								
Operating ambient temperature	— 10°C to + 50°C								
Conversation temperature	— 20°C to + 65°C								
Operating ambient humidity	20 to 90% RH (no condensation)								
Conversation humidity	5 to 95% RH (no condensation)								
Operation altitude	1000 m (3281 feet) max. above sea level								
Vibration resistance	Vibration frequency 10 to 500 Hz, total amplitude 1.52 mm (10 to 70 Hz), vibration acceleration 150 m/s ² (70 to 500 Hz), sweep time 15 min/cycle, 12 sweeps in each X, Y and Z direction.								
Impact resistance	500 m/s ² of acceleration for 11 ms with half-sine wave applying three times for X, Y, and Z axes each, 18 times in total.								
Insulation class	Class B (+130°C)								
Withstandable voltage	At normal temperature and humidity, no failure with 500 VAC @50/60 Hz applied for one minute between motor winding and frame.								At normal temperature and humidity, no failure with 1000 VAC @50/60 Hz applied for one minute between motor winding and frame.
Insulation resistance	At normal temperature and humidity, not less than 100 MΩ between winding and frame by 500 VDC megger.								
Protection grade	IP40								
Winding temperature rise	80 K max. (Based on Sanyo Denki standard)								
Static angle error	± 0.09°				± 0.054°	± 0.09°			
Thrust play *1	0.075 mm (0.003 in) max. (load: 0.35 N (0.08 lbs))	0.075 mm (0.003 in) max. (load: 1.5 N (0.34 lbs))	0.075 mm (0.003 in) max. (load: 5 N (1.12 lbs))	0.075 mm (0.003 in) max. (load: 4 N (0.9 lbs))	0.075 mm (0.003 in) max. (load: 5 N (1.12 lbs))	0.075 mm (0.003 in) max. (load: 5 N (1.12 lbs))	0.075 mm (0.003 in) max. (load: 4 N (0.9 lbs))	0.075 mm (0.003 in) max. (load: 10 N (2.25 lbs))	0.075 mm (0.003 in) max. (load: 10 N (2.25 lbs))
Radial play *2	0.025 mm (0.001 in) max. (load: 5 N (1.12 lbs))								
Shaft runout	0.025 mm (0.001 in)								
Concentricity of mounting pilot relative to shaft	φ 0.05 mm (φ 0.002 in)	φ 0.05 mm (φ 0.002 in)	φ 0.075 mm (φ 0.003 in)	φ 0.075 mm (φ 0.003 in)	φ 0.05 mm (φ 0.002 in)	φ 0.05 mm (φ 0.002 in)	φ 0.075 mm (φ 0.003 in)	φ 0.075 mm (φ 0.003 in)	φ 0.075 mm (φ 0.003 in)
Squareness of mounting surface relative to shaft	0.1 mm (0.004 in)	0.1 mm (0.004 in)	0.1 mm (0.004 in)	0.1 mm (0.004 in)	0.1 mm (0.004 in)	0.1 mm (0.004 in)	0.1 mm (0.004 in)	0.075 mm (0.003 in)	0.075 mm (0.003 in)
Direction of motor mounting	Can be freely mounted vertically or horizontally								
Motor model number	SH160	103H78	SH286	103H8922	SM286	103H712 -6	103H822 -6	103H8922 -63	1
Type	—					S1 (continuous operation)			
Operating ambient temperature	— 10°C to + 50°C					— 10°C to + 40°C			
Conversation temperature	— 20°C to + 65°C					— 20°C to + 60°C			
Operating ambient humidity	20 to 90% RH (no condensation)					95% max.: 40°C max., 57% max.: 50°C max.,			
Conversation humidity	5 to 95% RH (no condensation)					35% max.: 60°C max. (no condensation)			
Operation altitude	1000 m (3280 feet) max. above sea level								
Vibration resistance	Vibration frequency 10 to 500 Hz, total amplitude 1.52 mm (10 to 70 Hz), vibration acceleration 150 m/s ² (70 to 500 Hz), sweep time 15 min/cycle, 12 sweeps in each X, Y and Z direction.								
Impact resistance	500 m/s ² of acceleration for 11 ms with half-sine wave applying three times for X, Y, and Z axes each, 18 times in total.								
Insulation class	Class B (+130°C)				Class F (+155°C)	Class B (+130°C)			
Withstandable voltage	At normal temperature and humidity, no failure with 1000 VAC @50/60 Hz applied for one minute between motor winding and frame.				At normal temperature and humidity, no failure with 1500 VAC @50/60 Hz applied for one minute between motor winding and frame.				
Insulation resistance	At normal temperature and humidity, not less than 100 MΩ between winding and frame by 500 VDC megger.								
Protection grade	IP40				IP43				
Winding temperature rise	80 K max. (Based on Sanyo Denki standard)								
Static angle error	± 0.054°	± 0.09°							
Thrust play *1	0.075 mm (0.003 in) max. (load: 10 N (2.25 lbs))								
Radial play *2	0.025 mm (0.001 in) (load: 5 N (1.12 lbs))	0.025 mm (0.001 in) (load: 5 N (1.12 lbs))	0.025 mm (0.001 in) (load: 5 N (1.12 lbs))	0.025 mm (0.001 in) (load: 10 N (2.25 lbs))	0.025 mm (0.001 in) (load: 5 N (1.12 lbs))	0.025 mm (0.001 in) (load: 5 N (1.12 lbs))	0.025 mm (0.001 in) (load: 5 N (1.12 lbs))	0.025 mm (0.001 in) (load: 10 N (2.25 lbs))	0.025 mm (0.001 in) (load: 10 N (2.25 lbs))
Shaft runout	0.025 mm (0.001 in)								
Concentricity of mounting pilot relative to shaft	φ 0.075 mm (φ 0.003 in)								
Squareness of mounting surface relative to shaft	0.1 mm (0.004 in)	0.075 mm (0.003 in)	0.15 mm (0.006 in)	0.1 mm (0.004 in)	0.15 mm (0.006 in)	0.075 mm (0.003 in)	0.1 mm (0.004 in)	0.1 mm (0.004 in)	
Direction of motor mounting	Can be freely mounted vertically or horizontally								

*1 Thrust play: Shaft displacement under axial load.

*2 Radial play: Shaft displacement under radial load applied 1/3rd of the length from the end of the shaft.

Safety standards

Model Number: SM286 CE/UL marked models

CE (TÜV)	Standard category	Applicable standard
Low-voltage directives		EN60034-1, EN60034-5
UL	Acquired standards	File No.
UL	UL1004-1, UL1004-6	E179832
	UL for Canada	CSA C22.2 No.100

Model Number: 103H712 -6 0, 103H822 -6 0, 103H8922 -63 1 CE marked model

CE (TÜV)	Standard category	Applicable standard
Low-voltage directives		EN60034-1, EN60034-5

