

DOE laser, red, 635 nm, 5 mW

DOE214-635-5-6(10x22)
Order Number: 70125696

Main Parameters (*)	min	typ	max	Unit
Wavelength		635		nm
Optical Diode Power		5		mW
Operating Voltage	3	5	6	V DC
Operating Current	25	45	65	mA
Operating Temperature	-20		50	°C
Storage Temperature	-40		80	°C

Main Data

Warranty	1 years
----------	---------

Technical Parameters

Lifetime	> 3,000 h
RoHS	yes

Optical Parameters

Beam Shape	DOE
Laser Class	2M
Divergence	H - 1.0 mrad
Optics	acryl lense
Laser technology	Single Mode Diode
Protection Lens	yes
Focus	fixed

Electrical Parameters

Potential of Housing	VDD(+)
----------------------	--------

Mechanical Parameters

Size	Ø10x22 mm
Material	Brass
Cable length	100 mm
Wire type	26AWG, 0,14mm ²
Output Aperture	6 mm
Housing Color	black
Weight	8.5 g
Stripping of wire	5 mm

DOE

Alpha	34 °
a	60 mm
Diameter (without holder)	8 mm
Width (without Holder)	1 mm
Material	PMMA

(*) Over the complete operating temperature range

Features




Picture




Cable color

Ground		black	GND
positive		red	3 - 6, typ 5 V DC

Drawing



Safety Label



Valid Revision

| 25-FEB-2016