

## 3-sided wheeled container, load capacity 500 kg

Width x depth x height 720 x 815 x 1530 mm



### Application:

For safely and easily transporting and storing goods.

### Execution:

- High-quality powder-coated lateral grids and rear panel grid in gentian blue RAL 5010
- Wheeled platform made of HDPE plastic in jet black RAL 9005, with two horizontal and one diagonal reinforcement plate
- Two swivel castors and two fixed castors made of polypropylene, white, with thread guards, roller bearings
- Useful height of the lateral grids 1350 mm
- Capacity: 718.2 litres

### Advantage:

- Improves the flow of material and goods
- Optimised to make loading trucks more efficient
- Smooth movement and versatile



<b>Art. no.</b>	<b>50190 001</b>
<b>Brand</b>	PILSL
<b>Manufacturer Part Number</b>	1000000081
<b>Load-carrying capacity</b>	500 kg
<b>Width</b>	720 mm
<b>Depth</b>	815 mm
<b>Height</b>	1530 mm
<b>Width x depth x height</b>	720 x 815 x 1530 mm
<b>Number of fixed rollers</b>	2
<b>Number of steering rollers</b>	2
<b>Colour</b>	Gentian blue RAL 5010, Jet black RAL 9005
<b>Loading-surface width</b>	665 mm
<b>Loading-surface depth</b>	800 mm
<b>Loading surface width x loading surface depth</b>	665 x 800 mm
<b>With wheel lock</b>	No
<b>Material of loading surface</b>	Plastic
<b>Material of wheel</b>	PP - Polypropylene
<b>Wheel diameter</b>	108 mm
<b>Wheel width</b>	35 mm
<b>Surface</b>	Powder-coated
<b>Total stop optional</b>	No
<b>Made in</b>	Germany
<b>Gross Weight</b>	27.200 kg
<b>Product Group</b>	5AV