



LABFACILITY
TEMPERATURE & PROCESS TECHNOLOGY

Platinum Resistance Pt100 4 wire class B Resistance Thermometer with DIN B Head



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Pt100 probe with DIN B terminal head
- Class B, 4 wire connection
- Various probe available lengths
- 6.0mm diameter in 316 stainless steel
- With Stainless steel plug
- Sensor temperature rating -50°C to +450°C
- Conforms to IEC 751

Specifications

Sensor type:	Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 wire
Construction:	6.0mm diameter stem in 316 stainless steel
Termination:	IP67 DIN B connection head
Process connection:	Stainless Steel plug
Cable Entry:	PG16
Probe temperature range:	-50°C to +450°C (connection head @ 170°C)

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com

Probe DiaØ	Probe length	Order code
6.0mm	500mm	2816508