

## Electronic housing - ME MAX 22,5 2-2 DEV-KIT KMGY - 2202524

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DEV-KIT ME MAX: contains 1 x ME MAX 22,5 2-2 housing and pluggable connection technology (4x MSTBO with 4x MSTBT), supplied in individual parts

### Why buy this product

- ✓ Narrow housing with overall width of 22.5 mm
- ✓ Touch-proof, plug-in connection technology
- ✓ Optional perboard for soldering THT components by hand
- ✓ Connection of individual housing modules by means of the optional ME TBUS via DIN rail

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 141749
GTIN	4055626141749
Weight per Piece (excluding packing)	113.000 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### General

Housing type	Component housing
Housing material	Polyamide
Color	light gray

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

#### Dimensions

Length	99 mm
Constructional height	110 mm

# Electronic housing - ME MAX 22,5 2-2 DEV-KIT KMGY - 2202524

## Technical data

### Dimensions

Width	22.5 mm
-------	---------

### Technical data

Flammability rating according to UL 94	V0
--	----

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

Approvals

EAC

---

## Electronic housing - ME MAX 22,5 2-2 DEV-KIT KMGY - 2202524

### Approvals

Ex Approvals

---

### Approval details

EAC



B.01742

### Accessories

#### Additional products

PCB - ME MAX/16 2-2 TBUS DEV-PCB - 2202542

Perfboard for the ME-MAX DEV-KIT; for 4-pos. MSTBO header; ideal for manual soldering



---

Electronic housing - ME MAX TBUS BS KMGY - 2199650

Component housing, Color: light gray



---

Plug - ME 22,5 TBUS 1,5/ 5 VPE1 KMGY - 2202543

Bus connector to connect ME-MAX modules on the DIN rail; suitable for ME-MAX DEV-KITS; contains ME 22,5 TBUS 1,5/ 5

