

Drawer cabinet system 550 B with 5 SOFT-CLOSE drawers

Depth 550 mm, width 1022 mm

Application:


Particularly suitable for careful storage of delicate, sensitive tools and parts in drawers.

Execution:

- Solidly welded steel sheet construction
- Tilt-proof due to built-in individual drawer pull-out locking
- The drawers have high-quality Delrin rollers which means that they run quietly
- Drawers with slots all around for inserting compartment rails and dividers
- Perforated steel sheet base (25 mm hole spacing) for fastening and fixing components
- Aluminium grip handles with paper and cellophane strips and lateral cover caps

Advantage:

- The damping system brakes the drawer while closing; it closes the drawer smoothly and soundlessly by means of the self-closing mechanism
- Impact load on tools and parts stored in the drawer is reduced to a minimum due to the smooth-closing drawers
- High quality - made in Germany



Art. no.	50298 711
Brand	HK
Manufacturer Part Number	50298711
Number of drawers	5 PCS
Height	1036 mm
Width	1022 mm
Depth	550 mm
Height x width x depth	1036 x 1022 x 550 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	900 x 450 mm
Drawer with slots	Yes
Perforated drawer base	Yes
Load-carrying capacity per drawer	100 kg
Drawer surface	0.41 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	Yes
With single pull-out safety brake	Yes
Central locking	Yes
Material of cover panel	Wood, plastic-coated
Cabinet colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Functions	RFID possible
Model	B5 32/5
Overall surface	2.05 m ²
Lock type	DOM® locking system
Material	Sheet steel
Gross Weight	133.000 kg
Product Group	5BB

EAN

4053625403868