

product type designation



Antenna RF660A 865-868 EU

SIMATIC RF600 antenna RF660A 865-868 EU for use in EUR IP67, -25 to +75 °C, without cable .

suitability for operation

SIMATIC RF600

radio frequencies

transmission frequency	865 ... 868 MHz
antenna gain compared to spherical radiator	
• with circular radiation	7 dB

electrical data

impedance	50 Ω
polarization	Circular
antenna gain compared to spherical radiator	
• with circular radiation	7 dB
standing wave ratio (VSWR) / maximum	2
radiating angle of the antenna	
• horizontal	60°
• vertical	60°
type of electrical connection / of the antenna	RP-TNC
design of plug-in connection	male

mechanical data

material	PA 12
color	Pastel turquoise
mounting distance	
• relating to metal surfaces / recommended / minimum	0 m

ambient conditions

ambient temperature	
• during operation	-25 ... +75 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
protection class IP	IP67
shock resistance	according to EN 60068-2-27
shock acceleration	300 m/s ²
vibrational acceleration	1 m/s ²

design, dimensions and weights

width	313 mm
height	313 mm
depth	80 mm
net weight	1600 g
fastening method	4 screws M4 according to VESA 100, optional with articulated bracket by using antenna mounting kit

wire length / of antenna wire	0 m
product features, product functions, product components / general	
product feature / silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	CE (ETSI EN 302208)
certificate of suitability <ul style="list-style-type: none"> • IECEx 	No
reference code <ul style="list-style-type: none"> • according to IEC 81346-2 • according to IEC 81346-2:2019 	TF TFB
accessories	
accessories	Antenna cables 1 to 40 m
further information / internet-Links	
Internet-Link <ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	https://support.industry.siemens.com/cs/ww/en/view/67384964 http://www.siemens.com/ident/rfid https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
last modified:	11/3/2021 