

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878 Date first issue: 02/03/2020 Review date: 23/11/2020 Version: 2.1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture

: 2WORK DISINFECTANT SPRAY Product name

Product code : 2W07709

: Biocidal products (e.g. Disinfectants, pest Type of product

Product group control): Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Industrial/Professional use spec : Industrial

For professional use only

: Bactericide Use of the substance/mixture

Disinfectant

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

VOW FUROPE LTD 1ST FLOOR 1 EUROPA DRIVE SHEFFIELD, S9 1XT T: 0844 980 8000 WWW.VOWEUROPE.COM

1.4. Emergency telephone number

Country	Official advisory body	Address	Emergency number	Comment
Ireland	National Poisons Information Centre Beaumont Hospital	PO Box 1297 Beaumont Road 9 Dublin	+353 1 809 2566 (Healthcare professionals- 24/7) +353 1 809 2166 (public, 8am - 10pm, 7/7)	
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	Only for healthcare professionals

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Precautionary statements (CLP) : P102 - Keep out of reach of children.

P301+P330+P331 - IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing.

2.3. Other hazards

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII Contains no PBT/vPvB substances ≥ 0.1% assessed in accordance with REACH Annex XIII

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Didecyldimethylammonium Chloride	CAS-no: 7173-51-5 Einecs nr: 230-525-2 EG annex nr: 612-131-00-6	0.3	Acute Tox. 4 (Oral), H302 Skin Corr. 1B, H314 Eye Dam. 1, H318 Aquatic Acute 1, H400 (M=10) Aquatic Chronic 2, H411

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice : Never give anything by mouth to an unconscious person. If you feel unwell, seek medical

advice (show the label where possible).

Inhalation : Allow affected person to breathe fresh air. Allow the victim to rest.

Skin contact : Remove affected clothing and wash all exposed skin area with mild soap and water,

followed by warm water rinse.

Eye contact : Immediately flush eyes thoroughly with water for at least 15 minutes.

Ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Acute effects skin : mild skin irritation.

Acute effects eyes : May cause eye irritation. Redness.

Acute effects oral route : May cause irritation to the digestive tract.

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Use extinguishing media appropriate for surrounding fire. Water.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released. Carbon dioxide. Carbon monoxide.

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any

chemical fire. Prevent fire fighting water from entering the environment.

Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.

Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible.

Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Section 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or

smoking and when leaving work. Provide good ventilation in process area to prevent

formation of vapour.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a cool, well-ventilated place. Keep container tightly closed. Keep only in original

container.

Incompatible products : Strong acids. Oxidizing agent.

23/11/2020 (Revision date) EN (English) 2/6

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

No additional information available

8.2.2. Personal protection equipment

Personal protective equipment:

Avoid all unnecessary exposure.

8.2.2.1. Eye and face protection

No additional information available

8.2.2.2. Skin protection

Hand protection:

Wear protective gloves.

8.2.2.3. Respiratory protection

No additional information available

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid
Colour : Yellow.
Physical state/form : Liquid.

Odour : Characteristic.
Odour threshold : Not available

Melting point/range : 0 °C

Freezing point : Not available Boiling point/Boiling range : 100 °C

Flammability : Non flammable. Explosive limits : Not available Lower explosion limit : Not available Upper explosion limit : Not available Flash point : > 93 °C Autoignition temperature : Not available Decomposition temperature : Not available : 9.75 – 10.25 рΗ Viscosity, kinematic : Not available

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

: Soluble in water. Soluble in ethanol. Solubility

Partition coefficient n-octanol/water (Log Kow) : Not available Vapour pressure : Not available Vapour pressure at 50 °C : Not available Density : Not available

Relative density

: Not available Relative vapour density at 20 °C Particle characteristics : Not applicable

9.2. Other information

9.2.1. Information with regard to physical hazard classes

No additional information available

9.2.2. Other safety characteristics

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

Heat. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Oxidizing agent.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

: Not classified Acute toxicity (oral) : Not classified Acute toxicity (dermal) Acute toxicity (inhalation) : Not classified Skin corrosion/irritation : Not classified

pH: 9.75 - 10.25

Additional information : Based on available data, the classification criteria are not met

Serious eye damage/irritation : Not classified

pH: 9.75 - 10.25

: Based on available data, the classification criteria are not met Additional information

Respiratory or skin sensitisation : Not classified

Additional information : Based on available data, the classification criteria are not met

Germ cell mutagenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

Carcinogenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

Reproductive toxicity : Not classified

Additional information : Based on available data, the classification criteria are not met

STOT-single exposure : Not classified

Additional information : Based on available data, the classification criteria are not met

STOT-repeated exposure : Not classified

Additional information : Based on available data, the classification criteria are not met

Aspiration hazard

Additional information : Based on available data, the classification criteria are not met

11.2. Information on other hazards

11.2.1. Endocrine disrupting properties

No additional information available

23/11/2020 (Revision date) EN (English) 4/6

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

11.2.2. Other information

Potential adverse human health effects and

symptoms

: Based on available data, the classification criteria are not met

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, short-term

(acute)

Hazardous to the aquatic environment, long-term

(chronic)

: Not classified

: Not classified

Not rapidly degradable

Didecyldimethylammonium Chloride (7173-51-5)	
EC50 - Crustacea [1]	0.03 mg/l
EC50 96h - Algae [1]	0.06 mg/l

12.2. Persistence and degradability

	RA		1
 	ĸΔ	Δ	X

Persistence and degradability Biodegradable.

12.3. Bioaccumulative potential

ULTRA AX

Bioaccumulative potential No bioaccumulation.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

ULTRA AX

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

12.6. Endocrine disrupting properties

No additional information available

12.7. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations

: Dispose in a safe manner in accordance with local/national regulations.

Waste / unused products

: Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA

ADR	IMDG	IATA	
14.1. UN number or ID number			
Not regulated	Not regulated	Not regulated	
14.2. UN proper shipping name			
Not regulated	Not regulated	Not regulated	
14.3. Transport hazard class(es)			
Not regulated	Not regulated	Not regulated	
14.4. Packing group			
Not regulated	Not regulated	Not regulated	
14.5. Environmental hazards			
Not regulated	Not regulated	Not regulated	
No supplementary information available			

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Substances subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 july 2012 concerning the export and import of hazardous chemicals: Didecyldimethylammonium chloride (7173-51-5)

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Contains no substance subject to REGULATION (EU) No 1005/2009 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 September 2009 on substances that deplete the ozone layer.

Contains no substance subject to Regulation (EU) 2019/1148 of the European Parliament and of the Council of 20 June 2019 on the marketing and use of explosives precursors.

Contains no substance subject to Regulation (EC) 273/2004 of the European Parliament and of the Council of 11 February 2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE

COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and

amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:		
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4	
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1	
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2	
Eye Dam. 1	Serious eye damage/eye irritation, Category 1	
H302	Harmful if swallowed.	
H314	Causes severe skin burns and eye damage.	
H318	Causes serious eye damage.	
H400	Very toxic to aquatic life.	
H411	Toxic to aquatic life with long lasting effects.	
Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B	

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.