

Safety data sheet according to 1907/2006/EC, Article 31

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML
- **Article number:** 440.0071010.076
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Sector of Use**
 - SU21 Consumer uses: Private households / general public / consumers
 - SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC9a Coatings and paints, thinners, paint removers
- **Process category**
 - PROC7 Industrial spraying
 - PROC11 Non industrial spraying
- **Application of the substance / the mixture** Preparation
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
MOTIP DUPLI B.V.
Wolfraamweg 2
NL-8471 XC Wolvega
Nederland
Tel : +31 (0)561 694400
Fax: +31 (0)561 694411
e-mail: info@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:** +31 (0)561-694400 (09:00h - 17:00h)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.
STOT SE 3 H336 May cause drowsiness or dizziness.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS02



GHS07

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

(Contd. of page 1)

· **Signal word** *Danger*

· **Hazard-determining components of labelling:**

acetone

n-butyl acetate

butan-1-ol

· **Hazard statements**

H222-H229 *Extremely flammable aerosol. Pressurised container: May burst if heated.*H319 *Causes serious eye irritation.*H336 *May cause drowsiness or dizziness.*

· **Precautionary statements**

P101 *If medical advice is needed, have product container or label at hand.*P102 *Keep out of reach of children.*P210 *Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.*P211 *Do not spray on an open flame or other ignition source.*P251 *Do not pierce or burn, even after use.*P260 *Do not breathe spray.*P410+P412 *Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.*P501 *Dispose of contents / container in accordance with regional regulations.*

· **Additional information:**

EUH066 *Repeated exposure may cause skin dryness or cracking.*

· **2.3 Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· **3.2 Chemical characterisation: Mixtures**

· **Description:** Mixture of substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 67-64-1 EINECS: 200-662-2 Index number: 606-001-00-8 Reg.nr.: 01-2119471330-49	acetone ⚠ Flam. Liq. 2, H225 ⚠ Eye Irrit. 2, H319; STOT SE 3, H336	25-<50%
CAS: 115-10-6 EINECS: 204-065-8 Index number: 603-019-00-8 Reg.nr.: 01-2119472128-37	dimethyl ether ⚠ Flam. Gas 1, H220 Press. Gas C, H280	20-<25%
CAS: 123-86-4 EINECS: 204-658-1 Index number: 607-025-00-1 Reg.nr.: 01-2119485493-29	<i>n</i> -butyl acetate ⚠ Flam. Liq. 3, H226 ⚠ STOT SE 3, H336	12.5-<20%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21	propane ⚠ Flam. Gas 1, H220 Press. Gas C, H280	5-<10%
CAS: 108-65-6 EINECS: 203-603-9 Index number: 607-195-00-7 Reg.nr.: 01-2119475791-29	2-methoxy-1-methylethyl acetate ⚠ Flam. Liq. 3, H226	5-<10%

(Contd. on page 3)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

		(Contd. of page 2)
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32	butane (containing $\geq 0,1$ % butadiene (203-450-8)) Flam. Gas 1, H220 Press. Gas C, H280	5-<10%
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27	isobutane Flam. Gas 1, H220 Press. Gas C, H280	5-<10%
CAS: 71-36-3 EINECS: 200-751-6 Index number: 603-004-00-6 Reg.nr.: 01-2119484630-38	butan-1-ol Flam. Liq. 3, H226 Eye Dam. 1, H318 Acute Tox. 4, H302; Skin Irrit. 2, H315; STOT SE 3, H335-H336	<2.5%
CAS: 9004-70-0	cellulose nitrate Flam. Sol. 1, H228	<2.5%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture**
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters -**
- **Protective equipment:** Mouth respiratory protective device.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Mount respiratory protective device.
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

GB

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

(Contd. of page 3)

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**
 - Do not spray onto a naked flame or any incandescent material.
 - Keep ignition sources away - Do not smoke.
 - Keep respiratory protective device available.
 - Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
 - Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 2 B
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.

· 8.1 Control parameters

- **Ingredients with limit values that require monitoring at the workplace:**

67-64-1 acetone

WEL Short-term value: 3620 mg/m³, 1500 ppm
Long-term value: 1210 mg/m³, 500 ppm

115-10-6 dimethyl ether

WEL Short-term value: 958 mg/m³, 500 ppm
Long-term value: 766 mg/m³, 400 ppm

123-86-4 n-butyl acetate

WEL Short-term value: 966 mg/m³, 200 ppm
Long-term value: 724 mg/m³, 150 ppm

108-65-6 2-methoxy-1-methylethyl acetate

WEL Short-term value: 548 mg/m³, 100 ppm
Long-term value: 274 mg/m³, 50 ppm
Sk

106-97-8 butane (containing ≥0,1 % butadiene (203-450-8))

WEL Short-term value: 1810 mg/m³, 750 ppm
Long-term value: 1450 mg/m³, 600 ppm
Carc (if more than 0.1% of buta-1.3-diene)

71-36-3 butan-1-ol

WEL Short-term value: 154 mg/m³, 50 ppm
Sk

- **Additional information:** The lists valid during the making were used as basis.

· 8.2 Exposure controls

- **Personal protective equipment:**
- **General protective and hygienic measures:**
 - Keep away from foodstuffs, beverages and feed.
 - Immediately remove all soiled and contaminated clothing
 - Wash hands before breaks and at the end of work.
 - Do not inhale gases / fumes / aerosols.
 - Avoid contact with the eyes and skin.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

(Contd. of page 4)

Avoid contact with the eyes.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Protection of hands:**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

· Form:	Aerosol
· Colour:	Black
· Odour:	Solvent-like
· Odour threshold:	Not determined.

· **pH-value:** Not determined.

· **Change in condition**

· Melting point/freezing point:	Undetermined.
· Initial boiling point and boiling range:	Not applicable, as aerosol.

· **Flash point:** <0 °C (<32 °F)
Not applicable, as aerosol.

· **Flammability (solid, gas):** Not applicable.

· **Ignition temperature:** 240 °C (464 °F)

· **Decomposition temperature:** Not determined.

· **Auto-ignition temperature:** Product is not selfigniting.

· **Explosive properties:** Product is not explosive. However, formation of explosive air/ vapour mixtures are possible.

· **Explosion limits:**

· Lower:	1.2 Vol %
· Upper:	26.2 Vol %

· **Vapour pressure at 20 °C (68 °F):** 4,000 hPa (3,000.2 mm Hg)

· **Density at 20 °C (68 °F):** 0.76 g/cm³ (6.34 lbs/gal)

· **Relative density** Not determined.

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

(Contd. of page 5)

· Vapour density	Not determined.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	92.0 %
· EU-VOC:	704.7 g/l
· EU-VOC in %:	91.97 %
· Water:	0.3 %
· VOC (EC)	---
	704.7 g/l
· VOC-EU%	91.97 %
· Solids content:	9.6 %
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**

67-64-1 acetone

Oral	LD50	5,800 mg/kg (rat)
Dermal	LD50	>15,800 mg/kg (rabbit)
Inhalative	LC50 / 4h	76 mg/l (rat)

123-86-4 n-butyl acetate

Oral	LD50	10,800 mg/kg (rat)
Dermal	LD50	>17,600 mg/kg (rabbit)
Inhalative	LC50 / 4h	1.85 mg/l (rat)

108-65-6 2-methoxy-1-methylethyl acetate

Oral	LD50	8,530 mg/kg (rat)
Dermal	LD50	>5,000 mg/kg (rabbit)
Inhalative	LC50 / 4 h	>10,000 mg/m ³ (rat)

71-36-3 butan-1-ol

Oral	LD50	2,292 mg/kg (rat)
Dermal	LD50	3,430 mg/kg (rabbit)

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

(Contd. of page 6)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation**
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1 Toxicity

Aquatic toxicity:

67-64-1 acetone

LC50/96h	8,300 mg/l (fish)
EC50/96h	7,200 mg/l (algae)
LC50 / 48 h	8,450 mg/l (crustacean (water flea))

115-10-6 dimethyl ether

EC50 / 96 h	155 mg/l (algae)
LC50 / 48 h	>4,000 mg/l (daphnia magna)
LC50 / 96 h	>4,000 mg/l (fish)

123-86-4 n-butyl acetate

LC50 / 96 h	81 mg/l (fish)
-------------	----------------

108-65-6 2-methoxy-1-methylethyl acetate

EC50 / 48 h	>500 mg/l (daphnia magna)
LC50 / 96 h	100-180 mg/l (oncorhynchus mykiss / Regenbogenforelle)

71-36-3 butan-1-ol

LC50 / 96 h	1,376 mg/l (fish)
-------------	-------------------

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.

Additional ecological information:

General notes:

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

12.5 Results of PBT and vPvB assessment

- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

(Contd. of page 7)

· **European waste catalogue**

08 01 11*	waste paint and varnish containing organic solvents or other hazardous substances
-----------	---

15 01 04	metallic packaging
----------	--------------------

· **Uncleaned packaging:**

· **Recommendation:** Non contaminated packagings may be recycled.

SECTION 14: Transport information

· **14.1 UN-Number**

· **ADR, IMDG, IATA** UN1950

· **14.2 UN proper shipping name**

· **ADR** 1950 AEROSOLS
 · **IMDG** AEROSOLS
 · **IATA** AEROSOLS, flammable

· **14.3 Transport hazard class(es)**

· **ADR**



· **Class** 2.1 5F Gases.
 · **Label** 2.1

· **IMDG, IATA**



· **Class** 2.1
 · **Label** 2.1

· **14.4 Packing group**

· **ADR, IMDG, IATA** not regulated

· **14.5 Environmental hazards:** Not applicable.

· **14.6 Special precautions for user**

· **Danger code (Kemler):** Warning: Gases.
 · **EMS Number:** -
 · **Stowage Code** F-D,S-U
SW1 Protected from sources of heat.
SW22 For AEROSOLS with a maximum capacity of 1 litre:
Category A. For AEROSOLS with a capacity above 1 litre:
Category B. For WASTE AEROSOLS: Category C, Clear
of living quarters.
 · **Segregation Code** SG69 For AEROSOLS with a maximum capacity of 1 litre:
Segregation as for class 9. Stow "separated from" class 1
except for division 1.4. For AEROSOLS with a capacity
above 1 litre: Segregation as for the appropriate
subdivision of class 2. For WASTE AEROSOLS:
Segregation as for the appropriate subdivision of class 2.

· **14.7 Transport in bulk according to Annex II of Marpol and the IBC Code**

Not applicable.

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

(Contd. of page 8)

· Transport/Additional information:

· ADR

· Limited quantities (LQ)

1L

· Excepted quantities (EQ)

Code: E0

Not permitted as Excepted Quantity

Code: E0

Not permitted as Excepted Quantity

· Transport category

2

· Tunnel restriction code

D

· IMDG

· Limited quantities (LQ)

1L

· Excepted quantities (EQ)

Code: E0

Not permitted as Excepted Quantity

Code: E0

Not permitted as Excepted Quantity

· UN "Model Regulation":

UN 1950 AEROSOLS, 2.1

SECTION 15: Regulatory information

· 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

· Directive 2012/18/EU

· Named dangerous substances - ANNEX I None of the ingredients is listed.

· Seveso category P3a FLAMMABLE AEROSOLS

· Qualifying quantity (tonnes) for the application of lower-tier requirements 150 t

· Qualifying quantity (tonnes) for the application of upper-tier requirements 500 t

· REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3, 40

· National regulations:

· Other regulations, limitations and prohibitive regulations

· Substances of very high concern (SVHC) according to REACH, Article 57

None of the ingredients is listed.

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H228 Flammable solid.

H280 Contains gas under pressure; may explode if heated.

H302 Harmful if swallowed.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H335 May cause respiratory irritation.

H336 May cause drowsiness or dizziness.

· Abbreviations and acronyms:

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

(Contd. on page 10)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 44

Revision: 24.11.2017

Trade name: PLASTI-KOTE® QUICK DRY ACRYLIC WHITE RAL 9016 MATT 400 ML

(Contd. of page 9)

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Flam. Gas 1: Flammable gases – Category 1

Aerosol 1: Aerosols – Category 1

Press. Gas C: Gases under pressure – Compressed gas

Flam. Liq. 2: Flammable liquids – Category 2

Flam. Liq. 3: Flammable liquids – Category 3

Flam. Sol. 1: Flammable solids – Category 1

Acute Tox. 4: Acute toxicity – Category 4

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

· *** Data compared to the previous version altered.**

GB