

Fieldbus Gateway

RS-232 to PROFINET

EPGG001

Part Number



- Easy handling
- Gateway from RS-232/422/485 interfaces to PROFINET
- With two Industrial Ethernet ports

PROFINET

Technical Data

Electrical Data	
Supply Voltage	10...32 V DC
Current Consumption Gateway (U _b = 24 V)	< 100 mA
Temperature Range	0...55 °C
Short Circuit Protection	yes
Reverse Polarity Protection	yes
Overload Protection	yes
Interface	RS-232
Baud Rate RS-232	< 115200 Bd
Baud Rate PROFINET	< 100 MBd
Number of Bus Clients	512
Protection Class	III
Mechanical Data	
Material	Plastic PA
Weight	150 g
Degree of Protection	IP20
Connection Mode Supply Voltage	Terminal Block
Connection RS-Side	Terminal Block
Connection Bus Side	RJ45
DIN-Rail mounting	35 mm
PROFINET	●
Connection Table No.	42
Suitable Connection Equipment No.	74

These fieldbus gateways allow an easy connection of sensors and scanners to PROFINET.

Complementary Products

Software

