

# AT-GS950/48 48 port Gigabit WebSmart Switch

## AT-GS950/48-xx

48 port 10/100/1000T WebSmart switch with 4 SFP combo ports

#### Performance

Allied Telesis' WebSmart switch integrates the simplicity of unmanaged switches with the performance and reliability of managed switches to provide a cost-effective solution for users to integrate management at the edge of their network. This WebSmart switch provides a network manager some key features using the simple web-based management function such as; port-based VLANs, IEEE 802.1 p QoS, port trunking/link aggregation, port mirroring, priority queues and IEEE 802.1x security support. With support of up to 8K MAC addresses and a 512K packet buffer the AT-GS950/48 WebSmart switch is an ideal option for integrating management into your network solution.

## Value

Never thought you could afford managed switches in your network? Always wanted to provide management functionality at the edge? Now's your chance. Allied Telesis' WebSmart switch truely helps network managers get the most value for their dollar. With industry standard protocols, fiber media support via the SFP's and simple Plug and Play usability right out of the box how can you go wrong implementing this cost-effective solution into your network?

## **Quality and Reliability**

Allied Telesis

Allied Telesis is a worldwide leader in unmanaged Ethernet switches. Shipping more than 250,000 unmanaged switches each year, Allied Telesis offers proven reliability and industry recognized quality.

## **Key Features**

#### VLAN

- IEEE 802.1Q tagged
- Port-based
- Up to 64 groups

#### Quality of Service Classification

- IEEE 802.1p tagging
- Port-based priority
- Four priority queues per port

## IP Multicast Support (IPv4)

- IGMP snooping (v1/v2)
- Static multicast group
- Spanning-Tree, IEEE 802.1d/w

# IEEE 802.3ad Link Aggregation • Manual

#### IEEE 802.1x Port-based and MAC-based Network Access Control

- Local authentication server (MD5 only)
- Remote authentication through RADIUS
- Dynamic VLAN assignment
- RADIUS client for IEEE 802.1×
- DHCP client
- Statistics charts in Web
- Jumbo frames up to 9K

#### Others

- IEEE 802.3x flow control or \*HOL blocking Prevention (\*when flow control is off)
- Port mirroring
- Destination MAC filtering
- Ingress/egress rate limiting
- Broadcast storming control

## **Management Features**

#### Window-based Supporting

• Switch discovery management up to 254 switches

- Monitor list
- Trap view
- Device setting
- Firmware upgrade by FTP and Web
- Configuration back-up/restore by FTP
- Factory reset
- Password access control and restricted IP access list
- SNMPv1/v2c

#### MIBs

- RFC 1213 MIB-II
- RFC 1643 Ethernet MIB
- RFC 1493 Bridge MIB
- Private Enterprise MIB (Allied Telesis provides the spec)

## RMON Groups (1, 2, 3, 9)

- Stats
- History
- Alarms
  Events

# AT-GS950/48 | 48 port Gigabit WebSmart Switch

#### **Performance**

14,880pps for 10Mbps Ethernet
148,800pps for 100Mbps Ethernet
1,488,000pps for 1000Mbps Ethernet

MAC addresses	8K
Packet buffer	512KB
DRAM	32M
Flash	4M

#### **Power Characteristics**

Voltage	100-240V AC
Frequency	50/60Hz

## Interface Connections

10/100/1000T	RJ-45		
SFP	1000SX c	or	1000LX

## **Environmental Specifications**

Operating temp.	0°C to 40°C
	(32°F to I04°F)
Non-operating temp.	-25°C to 70°C
	(-13°F to 158°F)
Operating humidity	5% to 90% non-condensing
Storage humidity	5% to 95% non-condensing
Vibration	IEC 68-2-36
Shock	IEC 68-2-29
Drop	IEC 68-2-32
-	

# **Technical Specifications**

Physical	Characteristics
Dimensions	44.4cm x 32.2cm x 4.35cm
	17.5" x 12.7" x 1.7"

Weight 4.05kg (8.92 lbs)

Wall-mount or Desktop All units come with wall / 19" rack-mount brackets

# **Standards and Compliance**

IFEE	802.3	CSMA/CD
IEEE	802.3i	IOT
IEEE	802.3u	IOOTX
IEEE	802.3z	I OOOSX/LX
IEEE	802.3z/ab	1000T
IEEE	802.3x	Flow control
IEEE	802.lp	Prioritization (four queues)
IEEE	802.1x	Authentication
IEEE	802.1d	Bridging
IEEE	802.3ad	Link aggregation
IEEE	802.IQ	Tagged VLAN
IEEE	802.1d/w	Spanning-Tree
		Rapid Spanning-Tree

## **Electrical/Mechanical Approvals**

UL 1950 FCC/EN55022 Class A VCCI Class A C-Tick EN60950 (TUV) EN55024 CE CSA / CUL

#### MTBF

263,000 hours Bellcore TR332

## **Ordering Information**

#### AT-GS950/48-xx

48 port 10/100/1000T WebSmart switch with 4 SFP combo ports

Where xx = 10 for US power cord 20 for no power cord 30 for UK power cord 40 for Australian power cord 50 for European power cord

## **Product Contents**

Switch unit Rack-mount brackets and screws Power cord User manual/install guide on CD Rubber feet

USA Headquarters | 19800 North Creek Parkway | Suite 200 | Bothell | WA 98011 | USA | T: +1 800 424 4284 | F: +1 425 481 3895 European Headquarters | Via Motta 24 | 6830 Chiasso | Switzerland | T: +41 91 69769.00 | F: +41 91 69769.11 Asia-Pacific Headquarters | 11 Tai Seng Link | Singapore | 534182 | T: +65 6383 3832 | F: +65 6383 3830 www.alliedtelesis.com

© 2007 Allied Telesis Inc. All rights reserved. Information in this document is subject to change without notice. All company names, logos, and product designs that are trademarks or registered trademarks are the property of their respective owners. 617-000217 Rev. C

Connecting The (IP) World

