

## ESPRIMO Mobile V5515

Issue February 2008

Pages 3

The ESPRIMO Mobile V5515 is your gateway to professional mobile working. It is the professional companion for the price-conscious, casual user. This notebook is the ultimate balance of valuable performance and best-in-class mobility at very attractive prices.

You have the brilliant large 15.4-inch widescreen display for a maximum viewing comfort and an ergonomic full-size keyboard. Ideal for users working both on the road and in the office, it features a built-in super multi DVD writer and LAN. The Wireless LAN module offers unlimited freedom of connectivity wherever you are.

### Mobility

#### Valuable mobility at reasonable price

- Excellent price / performance ratio fits suiting all budgets
- Ready configured and constantly enhanced with latest technology

#### Convenient technology for mobile working

- Power-saving Intel® Processors
- Ideal connectivity through built-in Wireless LAN and LAN
- Ease of use through built-in super multi DVD burner

#### Robustness on the move

- German quality standards
- RoHS compliant for environmental friendly working
- Award-winning best-in-class manufacturing
- Mechanical and function stability through extensive quality tests

#### Ergonomics and flexibility in- and outside the office

- Enjoy the viewing quality of brilliant 15.4-inch WXGA TFT display
- Full-size keyboard for ergonomic working
- 3 x USB (2.0) ports for easy connectivity to all peripherals and external storage devices



System	ESPRIMO Mobile V5515
<b>Processor</b> <b>Intel® Celeron® M Processor</b> (Socket M) Second level cache Front side bus (FSB) <b>Intel® Core™ Duo Processor</b> Second level cache Front side bus (FSB) <b>Intel® Core™2 Duo Processor</b> (Socket M) Second level cache Front side bus (FSB)	530 (1.73 GHz) 1 MB 533 MHz up to T2450 (2.00 GHz) 2 MB 533 MHz up to T5500 (1.66 GHz) 2 MB 667 MHz
<b>Chipset</b> Northbridge Southbridge	SIS M672 SiS 968
<b>Memory</b> DIMM slots (667 MHz support) DDR2-667 SDRAM	2 up to 2 GB
<b>BIOS</b> BIOS Flash EPROM	Phoenix First BIOS
<b>Interfaces</b> Express card 34/54 USB 2.0 VGA Modem RJ-11 LAN RJ-45 Audio-in (line-in / microphone) Audio-out (line-out / headphone) DC-in Kensington Lock	1 3 1 optional 1 1 1 1 1
<b>Modem on board</b> 56K V.90 modem MDC1.5	optional
<b>LAN on board</b> built-in 10/100/1000 Mbps Fast Ethernet LAN (SiS196)	x
<b>Wireless Technologies (WLAN)</b> Import and usage according to country-specific regulations. Dual band antenna Atheros b/g	x
<b>Audio</b> Stereo speakers Sound chip Internal microphone	x Realtek ALC268 x
<b>Keyboard and pointing device</b> Keyboard Touchpad Status LED	87 keys, 19mm pitch, 2.5mm key stroke with two mouse buttons x
<b>Graphics</b> SiS Mirage 3+ Graphics, 64-256 MB shared memory	x
<b>Display</b> 15.4-inch TFT WXGA / 1280 x 800 pixel non-glare display, (glare optional) Max. resolution for external displays	x Up to 1920 x 1440 / true color / 60 Hz
<b>Hard disk drives (internal) *</b> S.M.A.R.T. 80 GB S-ATA 150 (5400 rpm) 120 GB S-ATA 150 (5400 rpm) 160 GB S-ATA 150 (5400rpm) 250 GB S-ATA 150 (5400rpm) * 1 Gbyte equals one billion bytes, when referring to hard disk drive capacity; accessible capacity may vary, also depending on used software and tool.	- x x x X
<b>Fixed drives</b> Super Multi DVD writer (incl DVD RAM, 8x double layer support)	x
<b>Manageability</b> Please refer to <a href="http://www.fujitsu-siemens.com/solutions/business_solutions/manageability/featurefinder.html">http://www.fujitsu-siemens.com/solutions/business_solutions/manageability/featurefinder.html</a> <b>Supported Standard</b> WMI / CIM / WBEM PXE BootP	- x -
<b>Security</b> <b>Physical security</b> Kensington Lock support <b>System Security</b> Norton Internet Security Symantec <b>User Security</b> User and supervisor BIOS password * for made4you customizing projects only	x x x
<b>Power supply</b> 1st Li-Ion battery 4 cell, 2000 mAh (29.6 Wh) First battery * (Mobile Mark 2002) [up to] AC adapter 20V/65W Adapter Rated voltage (AC input) 100 - 240 V Rated frequency 50 - 60 Hz DC output 20 V, 3.25 A * Battery life may vary depending on product model, configuration,	x 1h 20 min Up to 2h 30 min with accessory battery x

applications, power management settings and features utilized. Battery recharge time depends on usage. ** for made4you customizing projects only	
<b>Operating temperatures</b> Relative humidity (non-condensing) Ambient temperature	20% - 85% 5° - 35° C
<b>Dimensions / Weight</b> Dimensions (H x W x D) Weight* * Weight may vary depending on actual configuration	39 x 360 x 260 mm 2.7 kg
<b>Certificates</b> CE Marking R&TTE RoHS WHQL	x x x x
<b>Operating System</b> Microsoft Windows Vista™ (XP drivers available for download) Microsoft Windows Vista® Business/ Microsoft Windows XP® Professional TwinLoad	x x
<b>Software</b> (compatibility / preinstalled) Adobe Acrobat Reader Driver and Utility DVD (DUDVD) Easy Guide on-line user documentation Nero Norton Internet Security (incl. Firewall) 90days	x x x x x
<b>Accessories</b> (order number) AC-adapter Case Battery Memory 1GB-667 <a href="http://www.fujitsu-siemens.com/accessories/">http://www.fujitsu-siemens.com/accessories/</a>	S26391-F321-L400 Value case S26391-F119-L50 First Li-Ion battery 6 cells/ 5200 mAh, 56.1 Wh for up to 2.5h battery runtime S26391-F6120-L470 S26391-F6120-L481

This Data Sheet describes the highest configurations. The product is offered in fixed configurations which vary from country to country and edition to edition.