

LED machine lamp ring light

with adjustable magnetic feet



Application:

For use on drilling and milling machines

Execution:

- Attach to the machine by means of adjustable, rubber-coated magnetic feet
- High-performance LED 460 lumens in aluminium housing
- Uniform and low-reflection illumination, glare and flicker-free
- min. 50,000 hours service life
- Internal diameter 100 mm, external 160 mm, height 42 mm

Advantage:

- Simple, trouble-free mounting on the machine without any screws

Delivery:

With power supply



Art. no.	56879 300
Brand	BAUER & BÖCKER
Manufacturer Part Number	900/83
Power rating	7.5 W
Gross Weight	2.000 kg
Product Group	5ID

EAN

4260131238895