SPECIFICATIONS

Material: Boot: APM-RUBRGLAS (transparent silicone rubber) conforms to type ASTM D 1418. Frame: steel, zinc plated with chromate finish. Screws: SEELSKREWS (self-sealing screws), stainless steel with silicone rubber Oring

stainless steel with silicone rubber O-ring.

Temperature Range: E-SEELS: -80°F to +400°F

Pressure Range: Dust tight and splashproof.

Resistant to: Salt spray, weather, sunlight, ozone, corona and


most acids. **Shelf Life**: Excess of 25 years.

Operational Life: 10,000 actuations, minimum.

Notes:

- Mounting screws are supplied in lengths shown unless otherwise specified.
- 2. New sizes and types of RUBRGLAS-SEELS ® are being added regularly. Please request other types and styles as required.

Agency Recognition: Front Panel mounted Circuit Breaker Boots are UL-listed to UL Std. 50, types 1, 2, 3, 12, 12K, and 13. Back-of-Panel mounted Circuit Breaker boots are UL-listed to UL Std. 50, type 1. Also meet CSA standards.



ASSEMBLY CONSISTS OF 1 BOOT, MAT'L APM RUBRGLAS ®, 1 FRAME MAT'L C.R.S. ZINC PLATED WITH CHROMATE FINISH, & 2 #6-32 APM SEELSKREWS ® LENGTH = 3/8 UNLESS OTHERWISE SPECIFIED, DESIGNED TO MEET MIL-B-5423

TOLERANCES: UNLESS OTHERWISE NOTED ± 1/32

Н	CAD COMPUTER GENERATED					11-13-02
G	TRIGGER ADDED				M. MORSE	4-26-93
REV.			DESCRIPTION			DATE
MAXIMUM	AND MINIMUM MEASURE- E STATED DIRECTLY ON NSION.	ш	CIRCUIT BREAKER BOOT.	ENG.		
EACH DIME	NSION.	J⊒	TOGGLE, WIDE ANGLE, '	DWN.	J. PALUMBO	12-29-58
MAT'L: SI	LICONE RUBBER	⊨	TRANSPARENT (3 POLES)	CHKD.		
POLYMER TYPE ASTM D 1418		APM-HEXSEAL CORPORATION SCALE 9		COME S	·	
FINISH: GRADE 50				CT-1050		
TF	RANSPARENT			1:1 🖹		