

Column-mounted slewing jib crane PRAKTIKUS PS – complete set with compound anchor system and chain hoist

The reliable, affordable assistant for any workplace



Application:

Perfect entry-level crane

Execution:

- classification according to EN 13001 HC2 S2 HD2 for light industrial use
- power supply with round trailing cable
- lockable isolating switch
- Operating voltage: 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with manual sliding chassis – two-stage lifting speed
- Swivel range 270°
- **WITH DÜBEL MOUNTING SYSTEM VAS2 (simple installation and no foundation required)**

Advantage:

- Lightweight construction
- Perfect entry-level crane
- Cost-effective to assemble and rapid to commission thanks to a compound anchor system (no foundation or bottom casting)

Delivery:

Incl. detailed documentation



Art. no.	77111 049
Brand	VETTER
Manufacturer Part Number	PS10-3,0+VAS2+SIXX6F-H
Load-carrying capacity	1000 kg
Overhang	3000 mm
Construction height	3290 mm
Model	PRAKTIKUS PS
Lower edge of crane bottom	2500 mm
Max. lift height	1927 mm
Lifting device design	With electric chain hoist SIXX-HF
Mounting plate diameter	980 mm
Design	With electric chain hoist and VAS2
Height of hoist	573 mm
Stroke speed of precision hoist	1 m/min
Stroke speed of main hoist	4 m/min
Flange width	100 mm
Surface	Lacquered
Weight	404 kg
Operating voltage	400 V
Swivel range	270 Degree
Colour	Daffodil yellow RAL 1007
Max. vertical force	14 kN
Product category	B2B produkt
Gross weight	717 kg
Made in	Germany
Gross Weight	717.000 kg
Product Group	7EL