


RMB310



Absolute multiturn encoder with solid shaft

MULTITURN ENCODER WET LINE



1 M4 Depth 8 mm



Product characteristics

Resolution	65536 steps; 32768 revolutions; 31 bit
Communication interface	IO-Link
Shaft design	solid shaft
Shaft diameter [mm]	10

Application

Function principle	absolute
Revolution type	multiturn

Electrical data

Operating voltage [V]	18...30 DC; (to PELV)
Rated insulation voltage [V]	30
Current consumption [mA]	< 75
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	1000
Max. revolution electrical [U/min]	12000

Outputs

Short-circuit protection	yes
--------------------------	-----

Measuring/setting range

Resolution	65536 steps; 32768 revolutions; 31 bit
------------	--

Accuracy / deviations

Accuracy [°]	0.1
--------------	-----

Software / programming

Parameter setting options	preset; zero point; direction of rotation; rotational speed
---------------------------	---

RMB310



Absolute multiturn encoder with solid shaft

MULTITURN ENCODER WET LINE

Interfaces		
Communication interface	IO-Link	
Transmission type	COM3 (230,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Identification and Diagnosis; Switching Signal Channel; Measurement Data Channel (high resolution)	
SIO mode	no	
Required master port type	A	
Min. process cycle time [ms]	2.3	
IO-Link functions (cyclical)	function	bit length
	process value	96
	device status	4
	binary switching information	5
IO-Link functions (acyclical)	application specific tag; operating hours counter; internal temperature; switching cycles counter	
Supported DeviceIDs	Type of operation	IO-Link device ID
	Default	1064 d / 0x000428 h
Note	For further information please see the IODD PDF file at "Downloads"	
Operating conditions		
Ambient temperature [°C]	-40...85	
Storage temperature [°C]	-40...85	
Max. relative air humidity [%]	98; (condensation not permissible)	
Protection	IP 68; IP 69K	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD
	DIN EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	DIN EN 61000-4-6 HF conducted	10 V
Vibration resistance	DIN EN 60068-2-6	30 g / 10...1000 Hz half-sine
Shock resistance	DIN EN 60068-2-27	200 g / 6 ms
Continuous shock resistance	DIN EN 60068-2-29	30 g / 16 ms half-sine
Vibration resistance		30 g (10...1000 Hz)
MTTF [years]	283	

RMB310



Absolute multiturn encoder with solid shaft

MULTITURN ENCODER WET LINE

Mechanical data	
Weight [g]	472.1
Dimensions [mm]	Ø 42 / L = 65
Materials	flange: stainless steel (1.4401 / 316); housing: stainless steel (1.4404 / 444); plug: stainless steel (1.4401 / 316)
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	10
Shaft material	stainless steel (1.4112 / 440B)
Max. shaft load axial (at the shaft end) [N]	300
Max. shaft load radial (at the shaft end) [N]	300
Fixing flange	synchro-flange

Electrical connection - plug	
1	UB
2	SSC1.2 / IN
3	GND
4	IO-Link
5	n. c.

Connector: 1 x M12

