

## 24V Flexiprint Silicone IP67

RGB (PLCC6)

## **Specifications**

Voltage 24V Current 3x1A

Wattage 14.4W/m (3x4.8W/m)

Number of LED's 300pcs Length of Stripe 5m

Operating Temperature -25°~+60°C Storage Temperature -40°~+80°C Viewing Angle 110°

CE/RoHS compliant



Adhesive tape on backside IP67 Protection




## **Electrical and Optical Characteristics (Ta=25°C)**

Part Number	Colour	Wavelength / CCT	Intensity Im (typ.)	EEC
FPS-F02D-500	red	624nm	240	Е
	green	518nm	460	С
	blue	471nm	110	Е

Total: E

## **Dimensions**



Thickness: 5.9 mm

Thickness endings: 6.8 mm

250 mm 4pol Adaptercable included

not designed for submersion or outdoor usage IP protection is no longer applicable after cutting

- 1. All dimensions are in millimetres
- 2. Tolerance is  $\pm 0.25$ mm unless otherwise specified
- 3. Specifications are subject to change without notice

Please also take note of our **General Information for Flexiprint and LED Modules**