AP735 35W TO-263 Power Resistor GRCCL

- Power Dissipation 35 watts with heat sink
- Low inductance
- D²PAK housing
- Electrically isolated from backplate
- TCR Options ±100 ppm/°C
- RoHS Compliant



Characteristics

Tolerance (Code): \pm 1% (F), \pm 5% (J)

Value range: R02 to 130K (with standard resistance values)

Power rating: 35W at 25°C case temperature

Temperature coefficient: ± 100 ppm/°C Thermal resistance: 3.7°C/W

Inductance: 0.1µH maximum

Operating voltage: √P*R with a maximum of 250V

Dielectric strength: 2kVac Insulation resistance: $10G\Omega$


Operating temperature: -55°C to 155°C

Electrical Specifications

Parameter	Specification
Short term overload (2x Pr for R < 2Ω , 1.6 x Pr for R $\geq 2\Omega$, V < 1.5x operating voltage)	ΔR ±0.25%
Load life (1000 hours at rated power)	ΔR ±1.0%
Thermal shock (-55°C to 155°C, 5 cycles)	ΔR ±0.5%
Resistance to soldering heat (10 sec at 270°C)	ΔR ±0.5%
Vibration (20 G 10 - 2000Hz .06" D.A)	ΔR ±0.25%
Moisture sensitivity level	1

Soldering Profile

Power dissipation is 3.5W at an ambient temperature of 25°C when mounted on a double sided copper using FR4, $70\mu m$ of copper 39x30x1.6mm



ARCOL UK Limited,

Threemilestone Ind. Estate,

Truro, Cornwall, TR4 9LG, UK.

T +44 (0) 1872 277431

F +44 (0) 1872 222002

E sales@arcolresistors.com

www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. ARCOL operate a policy of continual product development, therefore, specifications may change.


It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask ARCOL.


Page 1 of 2 1/14.08

AP735 35W TO-263 Power Resistor




Dimensions (mm)






Recommended pad layout



Derating Curve



Ordering Procedure

Standard Resistor: Series, Resistance Value, Tolerance, Packaging options T&R - TR or Tubes - blank

e.g. AP735 8R2 J TR / AP735 2R F

ARCOL UK Limited,

Threemilestone Ind. Estate,

Truro, Cornwall, TR4 9LG, UK.

T +44 (0) 1872 277431

F +44 (0) 1872 222002

E sales@arcolresistors.com

www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. ARCOL operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask ARCOL.

1/14.08 Page 2 of 2