

**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**SV 100**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti Corrosion Products

### 1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.  
Ambersil House - Wylds Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

**Physical:** Aerosols, category 1  
Extremely flammable aerosol.  
Pressurised container: May burst if heated.

Classification is based on test data.

**Health:** Acute toxicity, category 4  
Harmful in contact with skin.  
Harmful if inhaled.  
Skin irritation, category 2  
Causes skin irritation.  
Eye irritation, category 2  
Causes serious eye irritation.

Classification based on calculation method.

**Environment:** Not classified

Classification based on calculation method.





**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

<b>Product identifier:</b>	Contains: xylene
<b>Hazard pictogram(s):</b>	 
<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H312 : Harmful in contact with skin. H332 : Harmful if inhaled. H315 : Causes skin irritation. H319 : Causes serious eye irritation.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area. P312 : Call a POISON CENTER or doctor/physician if you feel unwell. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
xylene		1330-20-7	215-535-7	30-60	Flam. Liq. 3, Acute Tox. 4, Acute Tox. 4, Skin Irrit. 2	H226,H332,H312,H315	A
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01-2119485926-20	68512-91-4	270-990-9	30-40	Press. Gas, Flam. Gas 1	H280,H220	K,G
acetone; propan-2-one; propanone	01-2119471330-49	67-64-1	200-662-2	10-30	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	A

**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

**Explanation notes**

A : substance with Community workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7) of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

(\* Explanation phrases : see chapter 16)

**SECTION 4: First aid measures****4.1. Description of first aid measures**

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with water for at least 15 minutes Seek medical advice
<b>Contact with skin :</b>	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical advice
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

<b>Inhalation :</b>	Harmful by inhalation. Symptoms : sore throat, cough, shortness of breath, headache
<b>Ingestion :</b>	May induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	Harmful in contact with skin Irritating to skin Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

**4.3. Indication of any immediate medical attention and special treatment needed**

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

**SECTION 5: Firefighting measures****5.1. Extinguishing media**

foam, carbon dioxide or dry agent

**5.2. Special hazards arising from the substance or mixture**

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO<sub>2</sub>



3 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Use only outdoors or in a well-ventilated area.  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Use only outdoors or in a well-ventilated area.  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

### 7.3. Specific end use(s)



**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

Anti Corrosion Products

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
<b>National established exposure limits, United Kingdom</b>			
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
		STEL	1500 ppm

### 8.2. Exposure controls

<b>Control procedures :</b>	Use only outdoors or in a well-ventilated area. Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. It is good practice to wear gloves and to provide adequate ventilation whenever using the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374). Use a reusable glove with a minimum breakthrough time of 30 minutes. The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	(butyl rubber)
<b>eyes :</b>	Wear safety eyewear according to EN 166.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Liquid under pressure.
<b>colour :</b>	Red.
<b>odour :</b>	Characteristic odor.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	Not available.

**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

**Flash point :** -17 °C (Closed Cup)  
**Evaporation rate :** Not available.  
**Explosion limits : upper limit :** Not available.  
**lower limit :** Not available.  
**Vapour pressure :** Not available.  
**Relative density :** 1.04 g/cm3.  
**Solubility in water :** Insoluble in water  
**Auto-ignition :** Not available.  
**Viscosity :** Not available.

## 9.2. Other information

# SECTION 10: Stability and reactivity

## 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

## 10.2. Chemical stability

Stable

## 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

## 10.4. Conditions to avoid

Avoid overheating

## 10.5. Incompatible materials

Strong oxidising agent

## 10.6. Hazardous decomposition products

CO,CO2

# SECTION 11: Toxicological information

## 11.1. Information on toxicological effects

**acute toxicity:** Harmful in contact with skin.  
Harmful if inhaled.  
**skin corrosion/irritation:** Causes skin irritation.  
**serious eye damage/irritation:** Causes serious eye irritation.  
**respiratory or skin sensitisation:** based on available data the classification criteria are not met  
**germ cell mutagenicity:** based on available data the classification criteria are not met



6 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

**carcinogenicity:** based on available data the classification criteria are not met  
**toxicity for reproduction:** based on available data the classification criteria are not met  
**STOT-single exposure:** based on available data the classification criteria are not met  
**STOT repeated exposure:** based on available data the classification criteria are not met  
**aspiration hazard:** based on available data the classification criteria are not met

#### Information on likely routes of exposure:

**Inhalation :** Harmful by inhalation.  
**Ingestion :** May cause gastrointestinal disturbances  
**Skin contact :** Harmful in contact with skin  
 Irritating to skin  
**Eye contact :** Irritating to eyes

#### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
acetone; propan-2-one; propanone	67-64-1	LD50 oral rat	> 5800 mg/kg
		LC50 inhal.rat	76 mg/l
		LD50 derm.rabit	> 15800 mg/kg

## SECTION 12: Ecological information

### 12.1. Toxicity

Not classified

### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
acetone; propan-2-one; propanone	67-64-1	IC50 algae	530 mg/l
		LC50 fish	5540 mg/l
		EC50 daphnia	8800 mg/l

### 12.2. Persistence and degradability

No information available

### 12.3. Bioaccumulative potential

No information available

### 12.4. Mobility in soil

Insoluble in water

### 12.5. Results of PBT and vPvB assessment



7 / 9

**CRC Industries UK Limited**  
 Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
 Somerset, TA6 4DD  
 Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

No information available

#### 12.6. Other adverse effects

No information available

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**Contaminated packaging :** Disposal should be in accordance with local, state or national legislation

### SECTION 14: Transport information

#### 14.1. UN number

UN-number : 1950

#### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

#### 14.4. Packing group

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203





**Productname :** SV 100  
**Ref.Nr.:** UDS000417\_3\_20170629 (EN)  
**Creationdate :** 29.06.17 Version : 2.0  
**Replaces:** UDS000417\_20150324

#### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H225 : Highly flammable liquid and vapour.  
H226 : Flammable liquid and vapour.  
H280 : Contains gas under pressure; may explode if heated.  
H312 : Harmful in contact with skin.  
H315 : Causes skin irritation.  
H319 : Causes serious eye irritation.  
H332 : Harmful if inhaled.  
H336 : May cause drowsiness or dizziness.

REVISIONS IN CHAPTRE : 8.2. Exposure controls  
acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistant bioaccumulative toxic  
vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.