

Cordless angle grinder L125 18.0-EC/5.0 SET

li-ion 18 V, 5 Ah

FLEX

Execution:

- With spindle lock
- Brushless motor with higher efficiency and longer service life
- with soft start, overload protection and power-on inhibitor
- electronic management system (EMS) to protect the machine and increase durability and efficiency

Delivery:

2x battery 18 V/5 Ah, charger 10.8/18.0 in L-BOXX, incl. protective cover, handle, face wrench, clamping flange and clamping nut



Art. no.	70379 025
Brand	FLEX
Manufacturer Part Number	417.947
Model	L 12518.0-EC/5.0
Battery included	Yes
Number of rechargeable batteries/batteries	2 PCS
Weight of rechargeable battery/battery	0.72 kg
Rechargeable battery/battery capacity	5 Ah
Battery voltage	18 V
Type of rechargeable battery/battery	Li-Ion
Motor design	Brushless motor
Nominal energy	90 Wh
Idle speed	8500 rpm
Washer diameter	125 mm
Thread dimension of spindle	M14
Tool holding device	M14
Weight	1.75 kg
With restart protection	Yes
With soft start	Yes
With overload protection	Yes
With speed pre-selection	No
With speed control	No
With battery capacity display	Yes
With quick clamping system	No
With reverse switch off	No
With disc brake	Yes
With dead man function	No
With working lights	No
Gross Weight	8.720 kg
Product Group	707