

# **APS-7000 Series**

500/1000 VA Programmable AC Power Source

# **FEATURES**

- 4.3" large LCD Display
- Measurement Function:
   Voltage, Current, Power, Frequency, Power Factor, Crest Factor,
   Apparent Power, Ipeak, Ipk hold
- Surge/Dip Control Mode
- Frequency: 45.0 ~ 500.0Hz (Std); 45.0 ~ 999.9Hz (Opt)
- Voltage Range (RMS): 155V (Std)/310V (Std)/600V (Opt)
- OCP/OTP/OHP Protection
- Simulate Mode, Sequence Mode, Program Mode
- Ramp Control Function
- ARB (Function Waveform) Mode
- . Standard Interface: USB/LAN
- Optional Interface: RS-232 & USB CDC/GPIB




The APS-7000 Series is an AC power source, containing abundant features for the testing and characteristic analysis of power supplies, electronic devices, components and modules. The APS-7000 Series is fully programmable to simulate different power outputs. All parameters and values as well as measurement results are displayed simultaneously on the 4.3 inch TFT-LCD screen.

The APS-7000 Series comprises nine measurement functions (Vrms, Irms, F, Ipk, W, VA, PF, Ipk hold, CF), and provides user interface similar to that of AC Power Meter. The APS-7000 Series, internal circuit design 4 sets of current range to improve measurement resolution, is ideal for the LED industry and standby mode power consumption test. Under the ARB (function waveform) mode, the APS-7000 Series provides waveforms, including SINE waveform, Triangle waveform, Staircase waveform, Clipped Sinewave, Crest factor waveform, Surge waveform, and Fourier series to meet the requirement of simulating abnormal input power waveform test of different industry.


Ten sets of Preset allow users to store ten settings; Power ON Output setting allows Sequence, Simulate, and Program to automatically execute output after the equipment power is on.

The APS-7000 Series features five methods to cope with special purpose or abnormal voltage, frequency, and phase; ten sets of the Simulate mode simulate power outage, voltage rise, and voltage fall; ten sets of the Sequence mode allow users to define parameters and produce sine wave by editing steps; Ramp Control allows users to set the variation speed for output voltage rise and fall; Surge/Dip Control simulates DUT's input power producing a Surge or Dip voltage overlapping with output voltage waveform at a specific time. Ethernet Port, on the rear panel of the series, can be used for remote program control; Sync Output Socket provides external 10V sync output; Signal Output Connector provides monitor of Program execution results. the APS-7000 Series also provides Trigger In/Out and Output on/off remote control functions from J1 connector on the rear panel.


## **APS-7050 Output Operating Area**



#### **APS-7100 Output Operating Area**




## A. SEQUENCE MODE



## Sequence Waveform


There are ten sets of Sequence mode and each set has  $0\sim255$  steps. The time setting range for each step is  $0.01\sim99.99$  seconds. Combining many sets of steps to edit required waveforms satisfies users' requirement of highly complicated waveforms.

## PROGRAM MODE




## Program Mode

This mode allows users to set ceiling and floor specifications to produce PASS/FAIL result after the measurement is done. It can also show test results for each test procedure or only show the last result. There are ten sets of Program mode and each set has 50 sets of memories. Each memory comprises 9 steps. Each Program will perform according to memories sequence, self-defined loops or designated steps to stop.







**Power Outage** 

**Voltage Rise** 

Voltage Fall


This mode can rapidly produce different simulated input transient waveforms such as power outage; voltage rise and voltage fall etc.

for engineers to evaluate the impact on DUT posed by the transient phenomena. For instance, capacitor endurance test.

# D. ARB MODE

This mode provides more than 50 different waveforms in 7 major categories to rapidly simulate distorted AC voltage waveforms.

Wave: TRIANGL




EXIT




Sine Waveform


Standard AC Waveform




Power harmonic output simulation is triangle waveform



Simulate square waveform and staircase waveform for commercial UPS







# **Clipped Sinewave**

Simulate grid power supply heavy load waveform

**Crest Factor Waveform** 

Simulate rectified filter current waveform by capacitor input

Surge Waveform

Simulate grid power supply's peak over-voltage



# Fourier Series Synthesized Waveform


Simulate real output power waveform. Distorted power waveform is produced due to output impedance and non-linear effect such as inductance, capacitance, and parasitic capacitance effect.


For example: motor.

Ramp control allows users to set output voltage rise or fall speed which is based on time (1ms) or voltage (1Vrms) unit.




Mode=Time, Tup=1 msec, VAC=100V, Freq=50Hz, Ramp output=on.






Mode=Voltage, Vdn=2Vrms, VAC=100V, Freq=50Hz, Ramp output=off.




# F. SURGE/DIP CONTROL



Overlapping a Surge/Dip voltage on a normal voltage as the input power for DUT allows users to simulate Surge/Dip situation and evaluate DUT characteristics.


# G. T IPEAK, HOLD FUNCTION



#### **Ipeak Measurement**

T, Ipk Hold sets delay time (1ms~60 seconds) for measurement after the output of Ipeak value and the maximum value will be retrieved. Update will be preceded only if measured value is greater than the original value. Ipk Hold is for measuring transient inrush current as soon as the equipment power is on that is usually done by oscilloscope and current probe. T, Ipk Hold delay time setting can be applied to measure inrush current of sequentially activated DUT.

# H. CONTROL PANEL CHARACTERISTICS



#### Standard Mode

There are two control panel modes: Standard mode and Simple mode. Both modes are shown as above. Standard mode combines settings and AC Power Meter measurement window display. Users

#### 

## Simple Mode

apply Function key (F1~F3) to select required measurement items. There are nine items for selection. Simple mode shows all measurement items on the display.





APS-7050 Front



APS-7100 Front



APS-7050 Rear Panel



APS-7100 Rear Panel

SELECTION GUIDE				
Model Name	Max. Output Current	Power Rating	Output Voltage	
APS-7050	4.2A/2.1A	500VA	0~310.0 Vrms	
APS-7100	8.4A/4.2A	1000VA	0~310.0 Vrms	

## **APPLICATIONS**

- The Broad Power Output Range of The Series is Ideal for Various Power Supply Manufacturers
- The Development of Electronic Components and Testing Applications for Manufacturers
- Incoming Quality Control and R & D Applications
- Small AC Current Measurement Applications

SPECIFICATIONS					
Model		APS-7050	APS-7100		
Power Rating		500VA	1000VA		
Output Voltage		0 ~ 310.0 Vrms	0 ~ 310.0 Vrms		
Output Frequency		45.00 ~ 500.0 Hz	45.00 ~ 500.0 Hz		
Maximum Current (r.m.s)	0~155Vrms	4.2A	8.4A		
	0~310Vrms	2.1A	4.2A		
Maximum Current (peak)	0~155Vrms	16.8A	33.6A		
	0~310Vrms	8.4A	16.8A		
Total Harmonic Distoration (THD)		≤0.5% at 45 ~ 500Hz (Resistive Load)			
Crest Factor	` '	≥4			
Line regulation 0.1% (% of full scale)					
Load regulation 0.5% (% of full scale)					
Response time		<100us			
SETTING					
Voltage	Range	155Vrms/310Vrms/Auto			
	Resolution	0.01V at 0.00 ~ 99.99Vrms; 0.1V at 100.0 ~ 310.0Vrms			
Frequency	Accuracy Range	±(0.5% of setting+2 counts) 45 ~ 500Hz			
rrequency	Resolution	0.01Hz at 45.00 ~ 99.99Hz/0.1Hz at 100.0 ~ 500.0Hz			
	Accuracy	±0.02% of setting			
Power On/Off Phase	Range	0 ~ 359°			
Angle	Resolution Accuracy	1° ±1°(45 ~ 65Hz)			
MEACHDEMENT	Accuracy	±1 (45 ~ 05112)			
MEASUREMENT Voltage(RMS)	Danas	0.20 20 751//20 76 77 50 1/27 51 155 01//155 1	270.01/		
Voltage(KIVIS)	Range Resolution	0.20 ~ 38.75Vrms/38.76 ~ 77.50 Vrms/77.51 ~ 155.0Vrms/155.1 ~ 310.0Vrms 0.01V at 0.00 ~ 99.99Vrms; 0.1V at 100.0 ~ 310.0Vrms			
	Accuracy	±(0.5% of reading + 2 counts)			
Frequency Range 45 ~ 500Hz					
manage /	Resolution	0.01Hz (at 45Hz~99.99Hz)/0.1Hz (at 100Hz~500.0Hz)			
	Accuracy	±0.1Hz			
Current(RMS)	<b>Range</b> 2.00 ~ 70.00mA/60.0 ~ 350.0mA/0.300 ~ 3.500A/3.00 ~ 17.5A				
	Resolution	0.01mA, 0.1mA, 0.001A, 0.01A			
e	Accuracy	$\pm$ (0.6% of reading+5 counts); 2.00~350.0mA/ $\pm$ (0.5% of reading+5 counts); 0.350~3.500A/ $\pm$ (0.5% of reading+3 counts); 3.500~17			
Current(Peak) Range 0.0 ~ 70.0A Resolution 0.1A					
	Accuracy				
Power(W)	Resolution				
	Accuracy	$\pm (0.6\% \text{ of reading} + 5 \text{ counts}); 0.20-99.99W; \pm (0.6\% \text{ of reading} + 5 \text{ counts}); 100.0 \sim 999.9W\pm (0.6\% \text{ of reading} + 2 \text{ counts}); 1000-9999W$			
Apparent(VA) Resolution 0.01VA, 0.1VA, 1VA,					
Power Factor	Accuracy ±(1% of reading + 5 counts);0.20~99.99VA/±(1% of reading + 5 counts);100.0~999.9VA/±(1% of reading + 2 co				
rower ractor	Power Factor         Range         0.000~1.000           Resolution         0.001				
	Accuracy	±(2% of reading + 2 counts)			
GENERAL	2000 (1 2000 (1)				
Remote Output Signal		Pass , Fail, Test-in Process, Trigger in, Trigger out , OUT ON / OF	F		
Sync Output Signal		Output Signal 10V, BNC type			
Number of Preset Protection		10(0~9 Numeric keys) OCP, OPP, OHP and Alarm			
SEQUENCE / SIMULATION / FUNCTION					
Number of Memories	•	10 (0 ~ 9 Numeric keys)			
Number of Steps		255 max. (For 1 sequence) 0.01 ~ 99.99S			
Step Time Setting Operation Within Step		Constant / Keep / Linear Sweep			
Parameters		Output Range, Frequency, Waveform (Sine Wave Only); On Phase, Off Phase, Term Jump Count (0 ~ 255)			
Sequence Control		jump-to, Branch 1, Branch 2, Trigger Output Start, Stop, Hold, Continue, Branch 1, Branch 2			
ENVIRONMENT CONDITIONS					
Operation Temperature	151116115	0 ~ +40°C			
Storage Temperature		-10 ~ +70°C			
Operating Temperature Storage Humidity		20 ~ 80% RH (No Condensation) 80% RH or less(No Condensation)			
PC REMOTE CONTROL INTERFACE					
Standard Interface		USB Host/LAN			
Optional Interface		GPIB/RS232 & USB CDC			
Input Power Source		1φ AC 115/230Vac ±15%			
DIMENSIONS					
		430(W) x 88(H) x 400(D) mm; Approx. 24Kg	430(W) x 88(H) x 560(D) mm; Approx. 38Kg		
			Specifications subject to change without notice. PA-7000GD1BI		

Specifications subject to change without notice.

OPTIONAL ASSESSORIES

APS-001 GPIB Interface Card

APS-002 RS-232/USB Interface Card GRA-423 APS-7000 Rack Mount Kit

**APS-003** Output Voltage Capacity :  $0 \sim 600 Vrms$ 

APS-004 Output Frequency Capacity: 45~999.9Hz

### **ORDERING INFORMATION**

APS-7050 500VA Programmable AC Power Source 1000VA Programmable AC Power Source

#### **ACCESSORIE**

CD ROM (User Manual, Programming Manual) x 1, Power Cord (Region Dependent), Mains Terminal Cover Set, GTL-123 Test Leads

Global Headquarters

GOOD WILL INSTRUMENT CO., LTD.

T +886-2-2268-0389 F +886-2-2268-0639

China Subsidiary

GOOD WILL INSTRUMENT (SUZHOU) CO., LTD.

T +86-512-6661-7177 F +86-512-6661-7277

T+31(0)40-2557790 F+31(0)40-2541194

Malaysia Subsidiary

GOOD WILL INSTRUMENT (M) SDN. BHD.

T +604-6309988 F +604-6309989 Europe Subsidiary

GOOD WILL INSTRUMENT EURO B.V.

U.S.A. Subsidiary

INSTEK AMÉRICA CORP.

T+1-909-399-3535 F+1-909-399-0819

Japan Subsidiary

TEXIO TECHNOLOGY CORPORATION.

T + 81 - 45 - 620 - 2305 F + 81 - 45 - 534 - 7181

Korea Subsidiary

GOOD WILL INSTRUMENT KOREA CO., LTD.

T +82-2-3439-2205 F +82-2-3439-2207



www.gwinstek.com