

SSSC clamp holder, positive, right-hand

for facing and longitudinal turning using SC indexable inserts

ATORN[®]

Application

for face and longitudinal turning with SC indexable insert 90°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

Advantage

- sturdy geometry for use in challenging conditions
- positive body geometry ensures low cutting forces
- excellent surface quality for medium infeed and finishing



Art. no.	17834 206
ISO name	SSSC R/L 2020 K09 IK G1/8
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	20 mm
Programming size	25 mm
Suitable for indexable inserts	SC.. 09T3..
Tool design	Left

EAN-Code

4050293449839