



SIMATIC DP, ET 200ECO PN, 8 AI (4 U/I + 4 RTD/TC); 8XM12, DEGREE OF PROTECTION IP67

Figure similar

General information	
Vendor identification (VendorID)	002AH
Device identifier (DeviceID)	0306H
Supply voltage	
Rated value (DC)	
• 24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, typ.	110 mA
Encoder supply	
Number of outputs	4
24 V encoder supply	
• short-circuit protection	Yes; Electronic at 1.4 A
• Output current, max.	1 A
Power losses	
Power loss, typ.	2.8 W
Analog inputs	
Number of analog inputs	8
• For voltage/current measurement	4
• For resistance/resistance thermometer measurement	4

permissible input voltage for voltage input (destruction limit), max.	28.8 V permanent, 35 V for max. 500 ms
Input ranges (rated values), voltages	
• 0 to +10 V	Yes
• 1 V to 5 V	Yes
• -10 V to +10 V	Yes
• -80 mV to +80 mV	Yes
Input ranges (rated values), currents	
• 0 to 20 mA	Yes
• -20 mA to +20 mA	Yes
• 4 mA to 20 mA	Yes
Input ranges (rated values), thermoelements	
• Type E	Yes
• Type J	Yes
• Type K	Yes
• Type N	Yes
Input ranges (rated values), resistance thermometer	
• Ni 100	Yes
• Ni 1000	Yes
• Ni 120	Yes
• Ni 200	Yes
• Ni 500	Yes
• Pt 100	Yes
• Pt 1000	Yes
• Pt 200	Yes
• Pt 500	Yes
Input ranges (rated values), resistors	
• 0 to 150 ohms	Yes
• 0 to 300 ohms	Yes
• 0 to 600 ohms	Yes
• 0 to 3000 ohms	Yes
Thermocouple (TC)	
Temperature compensation	
— Parameterizable	Yes
— internal temperature compensation	Yes
— external temperature compensation with compensations socket	Yes
Cable length	
• shielded, max.	30 m
Analog value creation	
Analog value display	SIMATIC S7 format
Measurement principle	integrating

Integration and conversion time/resolution per channel	
• Resolution (incl. overrange)	15 bits + sign
• Integration time, parameterizable	Yes
• Integration time (ms)	2/16.67/20/100 ms
• Interference voltage suppression for interference frequency f1 in Hz	500 / 60 / 50 / 10 Hz
• Conversion time (per channel)	4 / 19 / 22 / 102 ms
Smoothing of measured values	
• Parameterizable	Yes
• Step: None	Yes; 1 x cycle time
• Step: low	Yes; 4 x cycle time
• Step: Medium	Yes; 16 x cycle time
• Step: High	Yes; 64 x cycle time
Encoder	
Number of connectable encoders, max.	8
Connection of signal encoders	
• for voltage measurement	Yes
• for current measurement as 2-wire transducer	Yes
• for current measurement as 4-wire transducer	Yes
• for resistance measurement with two-wire connection	Yes
• for resistance measurement with three-wire connection	Yes
• for resistance measurement with four-wire connection	Yes
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	U: 0.0035%/°C; I:0.006%/°C; RTD: 0.0005%/°C; TC: 0.0035%/°C
Crosstalk between the inputs, min.	85 dB
Repeat accuracy in steady state at 25 °C (relative to input area), (+/-)	0.008 %
Interference voltage suppression for $f = n \times (f1 \pm 1 \%)$, f1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	46 dB
• Common mode interference, min.	70 dB
Interfaces	
Transmission procedure	100BASE-TX
Transmission rate, max.	100 Mbit/s
PROFINET IO	
• Number of PROFINET interfaces	1
• Autocrossing	Yes
• Automatic detection of transmission speed	Yes

• Integrated switch	Yes
PROFINET IO Device	
— IRT with the option "high flexibility" supported	Yes
— Prioritized startup	Yes
Protocols	
PROFINET IO	Yes
PROFINET CBA	No
Supports protocol for PROFI-safe	No
Protocols (Ethernet)	
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
• ping	Yes
• ARP	Yes
Interrupts/diagnostics/status information	
Status indicator	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnostic messages	
• Diagnostic functions	Yes
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes; Green "ON" LED
• Short circuit encoder supply	Yes; per module
• Group error	Yes; Red/yellow "SF/MT" LED
• Overflow/underflow	Yes
Galvanic isolation	
between the load voltages	Yes
between load voltage and all other switching components	No
between Ethernet and electronics	Yes
Galvanic isolation analog inputs	
• between the channels	No
Permissible potential difference	
between inputs and MANA (UCM)	10 Vpp AC
Isolation	
tested with	
• 24 V DC circuits	500 V
• Interface	1 500 V; According to IEEE 802.3
Degree and class of protection	

Degree of protection to EN 60529	
• IP65	Yes
• IP66	Yes
• IP67	Yes

Connection method	
M12	Yes

Dimensions	
Width	60 mm
Height	175 mm
Depth	49 mm

Weights	
Weight (without packaging)	930 g
last modified:	12.03.2015