

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINTOP® MSR-M-XL</b>	53112115 14.11.2013

For the benefits, refer to SKINTOP® MS-M-XL



Corrosion-resistant



Mechanical resistance



Optimum strain relief



Acid-resistant



Temperature-resistant



Variety of approval certifications



### Application range

With reducing seal insert, to seal cables with smaller outer diameters.

### Design

Metric connection thread acc. to EN 50262

### Norm references / Approvals

UL File Nr. E79903

### Note

Counter nut to be used: SKINDICHT® SM-M

Refer to SKINTOP® metric accessories for suitable accessories

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® MSR-M-XL	1 / 3
--------------------	-----------------------------	-------


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINTOP® MSR-M-XL</b>	<b>53112115</b> <b>14.11.2013</b>

### Technical Data

Article designation / size:	16 x 1,5
Clamping range ØF (mm):	2-7
SW (mm):	20
Overall length, C (mm):	37
Thread length, D (mm):	12
Pieces / PU:	50
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Note:	In stainless steel V2A available
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Protection rating:	Remark: A RoHS-non-compliant version is marketed under ÖLFLEX® 110 with VDE-REG.-Nr. 8067. To order this, please add appendix <1> to the below stated part numbers. This does not affect the above given further technical data or description. IP 69 K IP 68 - 10 bar
Temperature range:	Dynamic: -30 °C to +100 °C Fixed: -40 °C to +100 °C

Product Management	Document: SKINTOP® MSR-M-XL	2 / 3
--------------------	-----------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>SKINTOP® MSR-M-XL</b>	<b>53112115</b> <b>14.11.2013</b>



Product Management	Document: SKINTOP® MSR-M-XL	3 / 3
--------------------	-----------------------------	-------