


2 Double and triple pushbuttons

Selection diagram



Double and triple pushbuttons code structure

article		options																																									
Number of functions																																											
D double pushbutton T triple pushbutton																																											
Upper and lower pushbuttons		Ambient temperature																																									
A upper projecting, lower flush B upper projecting, lower projecting R upper flush, lower flush S upper flush, lower projecting		-25°C ... +85°C (standard) T6 -40°C ... +85°C																																									
Central element		Colour and markings																																									
C blanking plug (double pushbuttons only) L indicator light (double pushbuttons only) S projecting button (triple pushbuttons only)		<table border="1"> <thead> <tr> <th></th> <th>upper pushbutton</th> <th>central element</th> <th>lower pushbutton</th> </tr> <tr> <th>colour marking</th> <th>colour marking</th> <th>colour marking</th> <th>colour marking</th> </tr> </thead> <tbody> <tr> <td>0423</td> <td>green -</td> <td>white -</td> <td>red -</td> <td>-</td> </tr> <tr> <td>0221</td> <td>white -</td> <td>white -</td> <td>black -</td> <td>-</td> </tr> <tr> <td>0463</td> <td>green -</td> <td>blue -</td> <td>red -</td> <td>-</td> </tr> <tr> <td>0261</td> <td>white -</td> <td>blue -</td> <td>black -</td> <td>-</td> </tr> </tbody> </table>			upper pushbutton	central element	lower pushbutton	colour marking	colour marking	colour marking	colour marking	0423	green -	white -	red -	-	0221	white -	white -	black -	-	0463	green -	blue -	red -	-	0261	white -	blue -	black -	-												
	upper pushbutton	central element	lower pushbutton																																								
colour marking	colour marking	colour marking	colour marking																																								
0423	green -	white -	red -	-																																							
0221	white -	white -	black -	-																																							
0463	green -	blue -	red -	-																																							
0261	white -	blue -	black -	-																																							
Ring colour		<table border="1"> <thead> <tr> <th></th> <th>upper pushbutton</th> <th>central element</th> <th>lower pushbutton</th> </tr> <tr> <th>colour marking</th> <th>colour</th> <th>marking</th> <th>colour marking</th> </tr> </thead> <tbody> <tr> <td>AAAD</td> <td>green I</td> <td>white -</td> <td>red O</td> </tr> <tr> <td>AAAP</td> <td>green START</td> <td>white -</td> <td>red STOP</td> </tr> <tr> <td>AAAA</td> <td>white I</td> <td>white -</td> <td>black O</td> </tr> <tr> <td>AAAN</td> <td>white START</td> <td>white -</td> <td>black STOP</td> </tr> <tr> <td>AAAB</td> <td>black ↑</td> <td>white -</td> <td>black ↓</td> </tr> <tr> <td>AAAC</td> <td>black +</td> <td>white -</td> <td>black -</td> </tr> </tbody> </table>			upper pushbutton	central element	lower pushbutton	colour marking	colour	marking	colour marking	AAAD	green I	white -	red O	AAAP	green START	white -	red STOP	AAAA	white I	white -	black O	AAAN	white START	white -	black STOP	AAAB	black ↑	white -	black ↓	AAAC	black +	white -	black -								
	upper pushbutton	central element	lower pushbutton																																								
colour marking	colour	marking	colour marking																																								
AAAD	green I	white -	red O																																								
AAAP	green START	white -	red STOP																																								
AAAA	white I	white -	black O																																								
AAAN	white START	white -	black STOP																																								
AAAB	black ↑	white -	black ↓																																								
AAAC	black +	white -	black -																																								
		<table border="1"> <thead> <tr> <th></th> <th>upper pushbutton</th> <th>central projecting button</th> <th>lower pushbutton</th> </tr> <tr> <th>colour marking</th> <th>colour marking</th> <th>colour marking</th> <th>colour marking</th> </tr> </thead> <tbody> <tr> <td>AAAY</td> <td>green I</td> <td>red STOP</td> <td>green II</td> </tr> <tr> <td>AAAZ</td> <td>green ←</td> <td>red STOP</td> <td>green →</td> </tr> <tr> <td>AABD</td> <td>white →</td> <td>red STOP</td> <td>black ←</td> </tr> <tr> <td>AABA</td> <td>green ↑</td> <td>red STOP</td> <td>green ↓</td> </tr> <tr> <td>AABE</td> <td>white ↑</td> <td>red STOP</td> <td>black ↓</td> </tr> <tr> <td>AABF</td> <td>black ↑</td> <td>red STOP</td> <td>black ↓</td> </tr> <tr> <td>AABB</td> <td>green +</td> <td>red STOP</td> <td>green -</td> </tr> <tr> <td>AABC</td> <td>white +</td> <td>red STOP</td> <td>white -</td> </tr> </tbody> </table>			upper pushbutton	central projecting button	lower pushbutton	colour marking	colour marking	colour marking	colour marking	AAAY	green I	red STOP	green II	AAAZ	green ←	red STOP	green →	AABD	white →	red STOP	black ←	AABA	green ↑	red STOP	green ↓	AABE	white ↑	red STOP	black ↓	AABF	black ↑	red STOP	black ↓	AABB	green +	red STOP	green -	AABC	white +	red STOP	white -
	upper pushbutton	central projecting button	lower pushbutton																																								
colour marking	colour marking	colour marking	colour marking																																								
AAAY	green I	red STOP	green II																																								
AAAZ	green ←	red STOP	green →																																								
AABD	white →	red STOP	black ←																																								
AABA	green ↑	red STOP	green ↓																																								
AABE	white ↑	red STOP	black ↓																																								
AABF	black ↑	red STOP	black ↓																																								
AABB	green +	red STOP	green -																																								
AABC	white +	red STOP	white -																																								

Attention! The feasibility of a code number does not mean the effective availability of a product. Please contact our sales office.

2 Double and triple pushbuttons



Technical data

General

Protection degree:	IP67 according to IEC 60529
Ambient temperature:	-25°C +80°C
Mechanical endurance:	1 million operations cycles
Max operating frequency:	3600 operations cycles/hour
Actuating travel:	2,8 mm (NO contact), 1,4 mm (NC contact)
Actuating force:	5,5 N (1 NO contact) 4,6 N (1 NC contact) + 2,6 N (1 NO contact) + 1,7 N (1 NC contact)
Additional contact actuating force:	5 mm 2 ... 2,5 Nm
Maximum travel:	see page 61
Ring driving torque:	5 mm
Utilization requirements:	2 ... 2,5 Nm

In conformity with standards:

IEC 60947-1, IEC 60947-5-1, IEC 60204-1, EN 60947-1, EN 60947-5-1, EN 60204-1, UL 508, CSA 22-2 N°14

Main features

- 2 or 3 pushbuttons versions
- Protection degree IP67
- Illuminated version

⚠ Installation for safety applications:

Use only switches marked with the symbol . The safety circuit must always be connected with the **NC contacts** (normally closed contacts: 1-2) as stated in the standard EN 60947-5-1, encl. K, par. 2.

Markings and quality marks:



In conformity with requirements requested by:

Low Voltage Directive 2006/95/EC, Machinery Directive 2006/42/EC and Electromagnetic Compatibility 2004/108/EC.

Positive contact opening in conformity with standards:

IEC 60947-5-1, EN 60947-5-1, VDE 0660-206.

General characteristics

Shape

The new EROUND line double and triple pushbuttons are available in two shapes in order to suit any kind of application: projecting and flush. The possibility to choose shapes, colours and symbols allows various codes combinations.

Mechanical endurance

Thanks to their particular design Pizzato Eletrica double and triple pushbuttons guarantee a Mechanical endurance of more than 1.000.000 operations.

Illuminated version

A version with central indicator light is available for double pushbuttons.

Protection degree IP67


This series pushbuttons all have protection degree IP67, this way guaranteeing a total protection also in hard environmental conditions.

Temperature range extended



-40°C

Special versions can be ordered for use in environments where the temperature changes from +80°C to -40°C.

They can be installed inside cold stores, sterilizers or other equipments with very low ambient temperature. Special materials that have been used to realize these versions, maintain unchanged their features also in these conditions, widening the installation possibilities.

Double pushbuttons selection table

Actuator colour and marking		flush upper pushbutton flush central element flush lower pushbutton		flush upper pushbutton flush central element projecting lower pushbutton	
		black ring	satin chrome ring	black ring	satin chrome ring
	green pushbutton white indicator light red pushbutton "I"	E2 1PDR10423	E2 1PDR10423	E2 1PDSL10423	E2 1PDSL90423
	green pushbutton white indicator light "O" red pushbutton "START"	E2 1PDR1AAAD	E2 1PDR1AAAD	E2 1PDSL1AAAD	E2 1PDSL9AAAD
	green pushbutton white indicator light "STOP" red pushbutton "STOP"	E2 1PDR1AAAP	E2 1PDR1AAAP	E2 1PDSL1AAAP	E2 1PDSL9AAAP
	white pushbutton white indicator light "I"	E2 1PDR10221	E2 1PDR10221	E2 1PDSL10221	E2 1PDSL90221
	white pushbutton white indicator light "O"	E2 1PDR1AAAA	E2 1PDR1AAAA	E2 1PDSL1AAAA	E2 1PDSL9AAAA
	black pushbutton "START"	E2 1PDR1AAAN	E2 1PDR1AAAN	E2 1PDSL1AAAN	E2 1PDSL9AAAN
	black pushbutton "STOP"	E2 1PDR1AAAB	E2 1PDR1AAAB	E2 1PDSL1AAAB	E2 1PDSL9AAAB


Triple pushbuttons selection table

Actuator colour and marking		flush upper pushbutton projecting central pushbutton flush lower pushbutton		Actuator colour and marking		flush upper pushbutton projecting central pushbutton flush lower pushbutton	
		black ring	satin chrome ring	black ring	satin chrome ring	black ring	satin chrome ring
	"I" green pushbutton "STOP" red pushbutton "II"	E2 1PTRS1AAAY	E2 1PTRS9AAAY		"↑" white pushbutton "STOP" red pushbutton "↓"	E2 1PTRS1AABE	E2 1PTRS9AABE
	green pushbutton "←" green pushbutton "STOP" red pushbutton "→"	E2 1PTRS1AAAZ	E2 1PTRS9AAAZ		"↑" black pushbutton "STOP" red pushbutton "↓"	E2 1PTRS1AABF	E2 1PTRS9AABF
	green pushbutton "→" white pushbutton "STOP" red pushbutton "←"	E2 1PTRS1AABD	E2 1PTRS9AABD		"+"green pushbutton "STOP" red pushbutton "-"	E2 1PTRS1AABB	E2 1PTRS9AABB
	black pushbutton "↑" green pushbutton "STOP" red pushbutton "↓"	E2 1PTRS1AABA	E2 1PTRS9AABA		"+"white pushbutton "STOP" red pushbutton "-"	E2 1PTRS1AABC	E2 1PTRS9AABC

Items with code on the green background are available in stock


2 Double and triple pushbuttons

Double pushbuttons complete units




Actuator colour and marking		Contacts			flush upper button flush central element projecting lower button	
		pos 2	pos 3	pos 1	black ring	
	"I" green pushbutton black blanking plug "O" red pushbutton	1NC 	-	1NO	E2 AC-DXBC0601 E2 1PDSC1AAAK + E2 1BAC11 + E2 CP01G2V1 E2 CP10G2V1	

Triple pushbuttons complete units






Actuator colour and marking		Contacts			flush upper button projecting central pushbutton flush lower pushbutton	
		pos 2	pos 3	pos 1	black ring	
	"I" green pushbutton "STOP" red pushbutton "II" green pushbutton	1NO	1NC 	1NO	E2 AC-DXBC0801 E2 1PTRS1AAAY + E2 1BAC11 + E2 CP10G2V1 + E2 CP01G2V1 + E2 CP10G2V1	




Actuator colour and marking		Contacts			flush upper button flush central element projecting lower button	
		pos 2	pos 3	pos 1	black ring	
	"I" green pushbutton white indicator light "O" red pushbutton	1NC 	LED	1NO	E2 AC-DXBC0602 E2 1PDSL1AAAD + E2 1BAC11 + E2 CP01G2V1 + E2 LP1A2V1 + E2 CP10G2V1	


→ For the contact block and LED block characteristics see the respective chapters.

Dimensions**Flush double pushbutton****Projecting double pushbutton****Triple pushbutton**



All measures in the drawings are in mm

→ I2D and 3D files available on www.pizzato.com**Contacts maximum number**

Double pushbuttons E2 1PD series



Triple pushbuttons E2 1PT series

**Assembling minimum distances****Accessories**→ [ACCESSORIES at page 57](#)

All measures in the drawings are in mm

