

Flat spiral lathe chuck DURO-M DIN 6350, shape A

Hand chuck, for rear screw fittings



Application:

The Duro-M is a manually operated rotary lathe chuck with spiral ring and through hole. It is mainly used on conventional lathes for machining turned parts.

Execution:

- Chuck body (and all other components) made of steel
- Centric clamping
- High clamping force
- High concentricity
- Optimised for weight and mass inertia
- Minimum interference contour
- Three-jaw lathe chuck
- The Duro-M is also available with double jaw guide as an option.

Advantage:

- Workpieces with different clamping diameters can be clamped very quickly and without repositioning the jaws.
- Control edge
- Use on conventionally clamping, horizontal and vertical lathes as well as milling machines, rotary tables and dividers.

Delivery:

Ref. no. 22386011-22386072 Scroll lathe chuck 3-jaws with drilling and turning jaws

Ref. no. 22411021-22411081 Scroll lathe chuck 3-jaws with plain jaws and reverse top jaws.

The matching chuck key is included in the scope of delivery.



Art. no.	22411 051
Brand	RÖHM
Manufacturer Part Number	185313
Outer diameter	200
Number of jaws	3 PCS
DIN	6350-1
Clearance hole	55 mm
Pitch circle diameter	176
Centring diameter	160
Square width	11
Depth	4
Length 2	79.5 mm
Height	80.2 mm
Length	25.7 mm
Max. rotation speed	4000
Tension force	55
Max. torque	140 Nm
Weight	15.068 kg
Gross Weight	15.068 kg
Product Group	203

EAN

4019208526898