

3-point internal micrometer

ORION®

Application:

For measuring through-bores and short centring shoulders.

Execution:

- Scale with anti-glare, brushed chromium plated finish
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force

Delivery:

Single device with setting ring and measuring depth extension in a case



Art. no.	31910 062
Brand	ORION
Manufacturer Part Number	31910062
Min./max. length measuring range	62-75 mm
Measuring depth	114 mm
Error limit	5 µm
Vernier scale	0.005 mm
Extensions provided	150 mm
Measuring spindle increments	0.5 mm
Adjusting ring diameter	62 mm
Calibration Group	I, AC
DIN	863
Calibration Group Description	Internal micrometers (3 point)
Gross Weight	3.500 kg
Product Group	3BB

EAN

403924745955 1