

Han CGM-P F+B M25x1,5 D. 16-18 black



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 15 503 5199 |
| Specification | Han CGM-P F+B M25x1,5 D. 16-18 black |
| HARTING eCatalogue | https://b2b.harting.com/19155035199 |

Identification

| | |
|--------------------------|-------------|
| Category | Accessories |
| Series of hoods/housings | Han® F+B |
| Type of accessory | Cable gland |

Version

| | |
|---------------|---------------------|
| Pack contents | With spacing washer |
|---------------|---------------------|

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +100 °C |
| Wrench size | 32 |
| Degree of protection acc. to IEC 60529 | IP67 / IP69 |
| Size | M25 |
| Clamping range | 16 ... 18 mm |

Material properties

| | |
|--------------------------|--|
| Roughness of the surface | ≤0.8 µm |
| Colour (seal) | Blue |
| Material (cable glands) | Polyamide (PA) |
| Material (accessories) | VA 1.4305 |
| Colour (accessories) | Black |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |



Pushing Performance

Material properties

| | |
|-----------------------------|------|
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|-----------|------------------------|
| Approvals | Ecolab Topactive 200 |
| | Ecolab Topactive 500 |
| | Ecolab Topax 66 |
| | Ecolab Topactive OKTO |
| | Ecolab Topax 990 |
| | FDA 21 CFR 177.1500 |
| | FDA 21 CFR 176.170 (c) |
| | FDA 21 CFR 177.1390 |
| | FDA 21 CFR 177.1395 |
| | FDA 21 CFR 177.2600 |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 31.2 g |
| Country of origin | Germany |
| European customs tariff number | 39174000 |
| eCl@ss | 27144432 Screwed cable gland (electr.) |